

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19204-0017

Status:

Active

Overview:

Splices

Description:

Avikrimp™ 4 Way Splice for 14-16 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)


General	
Product Family	Splices
Series	19204
Comments	4 Way Connector
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Splices
Product Name	4 Way, Avikrimp™
UPC	800753051669

Physical	
Barrel Type	Closed
Color - Resin	Natural
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	5.372/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	4.32mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.30 - 2.00

Electrical	
Voltage - Maximum	600V

Material Info	
Old Part Number	B-5XC

Reference - Drawing Numbers	
Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19204-002



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19204Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
PremiumGrade™ Hand Crimp Tool	0640010100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION