

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19199-0010

Status:

Active

Overview:

Splices

Description:

Avikrimp™ Window Butt Connector for 14-16 AWG Wire, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-015 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

UPC

Splices

19199

Mil Spec M7928/5-4

Yes

M7928/5-4

Splices

Avikrimp™, Butt - Window

800753046832

Physical

Barrel Type

Color - Resin

Insulation

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Temperature Range - Operating

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

Blue

Nylon (PA)

Copper

Tin

Tin

2.192/g

Adhesive Tape on Reel

-55°C to +105°C

4.34mm

14, 16

1.00 - 2.50

Electrical

Voltage - Maximum

300V

Material Info

Old Part Number

WB-841T

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011, PS-19902-015

SD-19199-003



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19199Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880118

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION