


Duplex Fiber Optic Patch Cord

pro-SIGNAL

RoHS
Compliant



Dimensions : Millimetres

No.	Item	Qty.	Description
1.	Cable	1pc	Optical Fiber, Multi-Mode, 50/125, Duplex, \varnothing 1.8mm, Tight, Orange, PVC Jacket
2.	Connector		MTRJ, Female, Multi-Mode, Black Housing & Boot
3.	Connector	2pcs	ST, Simplex, Multi-Mode, Black Boot
5.	Heat Shrink Tube		Colour is Black

Notes:

1. New Products shall be reference to bellcore GR-326 standard
2. Insertion Loss : \leq 0.2dB Typical (1,300nm); MTRJ : \leq 0.7dB Typical (1,310nm)

Part Number Table

Description	Length (\pm A)	Part Number
Duplex fiber optic patch cord	2 \pm 0.05 Metre	SPC33500

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-SIGNAL