

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0212](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway™ Rubber Hand Lamp with Nylon Guard

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130102](#)
 NEMA Configuration N/A
 Outlet None
 Overview [Hand Lamps](#)
 Product Literature Order No 987650-8053
 Product Name Super-Safeway™
 Type Hand Lamps
 UPC 78678899200
 Woodhead Yes

Physical

Cord Length - Primary N/A
 Cord Length - Secondary N/A
 Depth 127.00mm (5.000")
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 400.05mm (15.750")
 Length N/A
 Material - Guard Nylon
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 240V

Material Info

Old Part Number 118



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130102Series](#)