

Sheathed RTD 100 Ω sensors with cable output

These 3-wire platinum probe sensors are sheathed in stainless steel 316L.

Temperature up to + 200 °C . Class B as per NFC 42-330

Reference	Diameter of sheath	Length of sheath	Type of cable	Cable length
L300114-507	6 mm	150 mm	PVC	2 m
L300114-510	6 mm	300 mm	PVC	2 m
L301114-507	6 mm	150 mm	silicon	2 m
L301114-510	6 mm	300 mm	silicon	2 m
L301214-507	6 mm	150 mm	PTFE	2 m
L301214-510	6 mm	300 mm	PTFE	2 m
P07.6041.09	6 mm	100 mm	PTFE	2.5 m
P07.6041.12	6 mm	200 mm	PTFE	1.5 m
P07.6041.48	3 mm	60 mm	PTFE	1 m
P07.6040.28	10 mm	135 mm	silicon + stainless steel braid	1 m
P07.6040.30	10 mm	230 mm	silicon + stainless steel braid	1 m
P07.6040.95	10 mm	165 mm	silicon + stainless steel braid	1 m
P07.6040.97	10 mm	265 mm	silicon + stainless steel braid	1 m
P07.6040.98	10 mm	265 mm	silicon + stainless steel braid	2.5 m

Temperature up to + 450 °C . Class A as per NFC 42-330

Reference	Diameter of sheath	Length of sheath	Type of cable	Cable length
L330111-506	1.6 mm	100 mm	PVC	2 m
L330111-509	1.6 mm	250 mm	PVC	2 m
L330112-506	3.2 mm	100 mm	PVC	2 m
L330112-509	3.2 mm	250 mm	PVC	2 m
L330114-506	6 mm	100 mm	PVC	2 m
L330114-508	6 mm	200 mm	PVC	2 m
L330114-514	6 mm	500 mm	PVC	2 m

Sheathed RTD 100 Ω sensors with a Souriau connector output

This 3-wire platinum probe sensor is sheathed in stainless steel 316L.

Temperature up to + 450°C . Class A as per NFC 42-330

Reference	Diameter of sheath	Length of sheath	Mounting with threading
L330310-004	4 mm	60 mm	M 18 x 150

Souriau extension piece

L126010-000	3 pins with cable clamp (without cable)
-------------	---