

Datasheet

Art.No. 96.032.4153.1

Male connector with strain relief RST20I3S S1 ZR2 V SW

Connector RST20i3, 3 pole, male, screw connection, 250V/20A, for cable diameters 10-14 mm, color of coding: black, color of housing: black



Art.No.	96.032.4153.1
EAN	4015573769724
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	L, N, PE

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	male
Number of poles	3
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide
------------------	-----------

Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

