



Storage Rack for HIS-Boxes

• HIS-Service Station

HIS general purpose heat shrink tubing provides a reliable insulation and protects against corrosion and mechanical influences. The handy dispenser is ideal for small and medium size projects on-site. The sturdy metal HIS Service Station comes with a cutter and can store all sizes and colours. The Service Station can be mounted to the wall in the work shop or service-van.

Features and Benefits

- Contains up to 5 dispenser boxes
- Place on bench or mount to wall
- Special cutter included for easily cutting tubing length to size



HIS-Service Station contains 5 dispensers and a special cutter.

TYPE	Description	Article-No.
HIS Service Station	HIS-Service Station incl. cutter, contents: 5 dispensers HIS-3 (shrink ratio: 3:1), black, sizes are as follows: HIS-3/1, HIS-6/2, HIS-12/4 (2 pcs.), HIS-24/8	365-30100
	HIS-Service Station incl. cutter, contents: 5 dispensers HIS-Pack (shrink ratio: 2:1), black, sizes are as follows: HIS-1/8, HIS-3/16, HIS-1/4, HIS-3/8, HIS 1/2 and one RiteOn Starter Pack	365-20000
	HIS-Service Station incl. cutter, empty	300-30000

All dimensions in mm. Subject to technical changes.

Heat Shrinkable Tubing 2:1 on a Reel

• HIS-PACK

- General purpose electrical insulation
- Protection against corrosion and mechanical abrasion

Features and Benefits

- Cross-linked Polyolefin, thin-wall and flexible
- Handy dispenser box including table showing application size range
- Available in black, red, blue, transparent and yellow/green
- 10 sizes from 1.2 mm to 25.4 mm



HIS-Pack.



Heat Shrinkable Tubing 2:1

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	2:1
Operating Temperature	-55 °C to +125 °C
Minimum Shrink Temperature	+100 °C
Longitudinal change after shrinkage	+/-5%
Dielectric Strength	20kV/mm according to ASTM D2671
Flammability	UL224 VW-1 (except clear)
Specifications	SAE - AMS - DTL-23053/5 Class 1 and 3, SAE - AMS - DTL-23053/5 Class 2 (clear), UL224 125 °C 600V VW-1



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.





Heat Shrinkable Tubing 2:1 on a Reel

- HIS-PACK

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Article-No.
HIS-PACK-1.2/0.6	1.2	0.6	0.40	10 m	Black (BK)	300-30120
	1.2	0.6	0.40	10 m	Blue (BU)	300-30126
	1.2	0.6	0.40	10 m	Red (RD)	300-30122
	1.2	0.6	0.40	10 m	Transparent (CL)	300-30123
HIS-PACK-1.6/0.8	1.6	0.8	0.40	10 m	Black (BK)	300-30160
	1.6	0.8	0.40	10 m	Blue (BU)	300-30166
	1.6	0.8	0.40	10 m	Red (RD)	300-30162
	1.6	0.8	0.40	10 m	Transparent (CL)	300-30163
HIS-PACK-2.4/1.2	2.4	1.2	0.50	10 m	Black (BK)	300-30240
	2.4	1.2	0.50	10 m	Blue (BU)	300-30246
	2.4	1.2	0.50	10 m	Red (RD)	300-30242
	2.4	1.2	0.50	10 m	Transparent (CL)	300-30243
HIS-PACK-3.2/1.6	3.2	1.6	0.50	10 m	Black (BK)	300-30320
	3.2	1.6	0.50	10 m	Blue (BU)	300-30326
	3.2	1.6	0.50	10 m	Green-Yellow (GNYE)	300-30327
	3.2	1.6	0.50	10 m	Red (RD)	300-30322
	3.2	1.6	0.50	10 m	Transparent (CL)	300-30323
HIS-PACK-4.8/2.4	4.8	2.4	0.50	10 m	Black (BK)	300-30480
	4.8	2.4	0.50	10 m	Blue (BU)	300-30486
	4.8	2.4	0.50	10 m	Green-Yellow (GNYE)	300-30487
	4.8	2.4	0.50	10 m	Red (RD)	300-30482
	4.8	2.4	0.50	10 m	Transparent (CL)	300-30483
HIS-PACK-6.4/3.2	6.4	3.2	0.60	5 m	Black (BK)	300-30640
	6.4	3.2	0.60	5 m	Blue (BU)	300-30646
	6.4	3.2	0.60	5 m	Green-Yellow (GNYE)	300-30647
	6.4	3.2	0.60	5 m	Red (RD)	300-30642
	6.4	3.2	0.60	5 m	Transparent (CL)	300-30643
HIS-PACK-9.5/4.7	9.5	4.7	0.60	5 m	Black (BK)	300-30950
	9.5	4.7	0.60	5 m	Blue (BU)	300-30956
	9.5	4.7	0.60	5 m	Green-Yellow (GNYE)	300-30957
	9.5	4.7	0.60	5 m	Red (RD)	300-30952
	9.5	4.7	0.60	5 m	Transparent (CL)	300-30953
HIS-PACK-12.7/6.4	12.7	6.4	0.60	5 m	Black (BK)	300-31270
	12.7	6.4	0.60	5 m	Blue (BU)	300-31276
	12.7	6.4	0.60	5 m	Green-Yellow (GNYE)	300-31277
	12.7	6.4	0.60	5 m	Red (RD)	300-31272
	12.7	6.4	0.60	5 m	Transparent (CL)	300-31273
HIS-PACK-19.1/9.5	19.1	9.5	0.80	5 m	Black (BK)	300-31900
	19.1	9.5	0.80	5 m	Blue (BU)	300-31906
	19.1	9.5	0.80	5 m	Green-Yellow (GNYE)	300-31907
	19.1	9.5	0.80	5 m	Red (RD)	300-31902
	19.1	9.5	0.80	5 m	Transparent (CL)	300-31903
HIS-PACK-25.4/12.7	25.4	12.7	0.90	5 m	Black (BK)	300-32540
	25.4	12.7	0.90	5 m	Blue (BU)	300-32546
	25.4	12.7	0.90	5 m	Green-Yellow (GNYE)	300-32547
	25.4	12.7	0.90	5 m	Red (RD)	300-32542
	25.4	12.7	0.90	5 m	Transparent (CL)	300-32543

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.