

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19164-0081
Status: Active
Overview: Perma-Seal™ Terminals
Description: Perma-Seal™ Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series 19164
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Perma-Seal™ Terminals
Product Name Perma-Seal™
Type Ring
UPC 800753113657

Physical

Barrel Type Closed
Insulation NiAc™
Material - Plating Mating Tin
Net Weight 4.492/g
Packaging Type Bag
Stud Size 1/4" (M6)
Wire Insulation Diameter 9.53mm
Wire Size AWG 8
Wire Size mm² 7.96

Material Info

Old Part Number SD-651-14

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing SD-19164-023



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19164Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640013900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640055400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION