



Sample photo

Order symbol: PC 100/60 HG
Product nbr: 6011301
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022042
El. number:
Finland: 3420311
Electric No. Denmark: 8212022030
Electric No. Italy: 7351025
Electric No. Sweden: 2535512

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
mm:	130	80	60	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	2.4	MIN 10	DIN-15 Mounting rail
				MIV 5	DIN-35 Mounting rail
				MIV 10	DIN-35 Mounting rail
Materials:				FP A 100/130	Front plate (Aluminium)
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Polyamide				
Cover colour:	RAL 7035 -light grey				
Cover screws colour:	Grey				
Gasket material:	TPE				
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
MIV 100	Mounting plate (Galvanized steel)			Flammability Rating: UL 746C 5V	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

