



Sample photo

Order symbol: PC 100/60 HT
Product nbr: 6011901
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022288
El. number:
Finland: 3420421
Electric No. Denmark: 8212022331
Electric No. Italy: 7352025
Electric No. Sweden: 2535612

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	130	80	60	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	2.4	MIN 10	DIN-15 Mounting rail
				MIV 5	DIN-35 Mounting rail
				MIV 10	DIN-35 Mounting rail
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Polyamide				
Cover colour:	Smoked grey				
Cover screws colour:	Black				
Gasket material:	TPE				
Temperatures:					
Temperature °C (short term):	-40 ... 120 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MIV 100	Mounting plate (Galvanized steel)				

