



Sample photo

Order symbol: PC 125/60 HG
Product nbr: 6011307
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022103
El. number:
Finland: 3420331
Electric No. Denmark: 8212022098
Electric No. Italy: 7351055
Electric No. Sweden: 2535530

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	130	130	60	MIN 10	DIN-15 Mounting rail
inch:	5.1	5.1	2.4	MIV 10	DIN-35 Mounting rail
			FP A 125/130	Front plate (Aluminium)	
			HFP 130	Front plate hinge series	
			FP 22046	Wall fastening lug (4 pcs)	
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/67		
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08		
Cover screws material:	Polyamide		Electrical insulation: Totally insulated		
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1		
Cover screws colour:	Grey		UV resistance: UL 508		
Gasket material:	TPE		Flammability Rating: UL 746C 5V		
Temperatures:			Glow Wire Test (IEC 695-2-1) °C: 960		
Temperature °C (short term):	-40 ... 120 °C		NEMA Class: NEMA 1, 4, 4X, 6		
Temperature °C (continuous):	-40 ... 80 °C		Certificates:		
Temperature °F (short term):	-40 ... 250 °F		Germanischer Lloyd (GL)		
Temperature °F (continuous):	-40 ... 175 °F		SGS Fimko		
Accessories:			Gost R		
MIV 125	Mounting plate (Galvanized steel)				

