



## Datasheet for part number DEMAM9SNMBK52

|  |  |
|--|--|
| Our Catalog Part Number: DEMAM-9S-NMBK52 |  |
| Brand: Cannon                            | Product Category: D Sub   Product Line: D Sub   Series: D*MA |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | D*M High reliable D-Sub Connectors with crimp termination |
| Wire Gauge Range AWG            | Standard: AWG 20-28. High Density: AWG 22-28              |
| Mating Cycles                   | 500   |
| Contact Arrangement             | 9 contacts size 20  |
| Dielectric Withstanding Voltage | 1000 VAC at sea level                                     |
| Current Rating                  | 7.5 A max   |
| Contact Resistance              | 10 milli Ohm max  |
| Operating Temperature           | -55°/+150°  |
| Salt Spray Test                 | 48 hours {96 Hrs for Stainless Steel}                     |
| Shell Material                  | steel   |
| Shell Finish                    | 50 microinch gold over 100 microinch copper               |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black   |
| Gender                          | Socket  |
| Contact Type                    | Crimp   |
| Contact Material                | copper alloy  |
| Contact Finish                  | gold over nickel (Performance Class 2)                    |
| Hardware                        | .120" (3,05mm) Through Hole                               |