

19" CABINETS

CamRack-LX 600 Wide

Flat packed-Quick Assembly in **5 minutes!**

19" Modular cabinets, 600mm wide, designed for cabling, telecommunications, IT and industrial.

- Delivered flat packed for ease of access to all installations. Also reduces associated logistic costs and offers greater protection during transit
- Aluminium profile external structure with diecast high resistance corners.
- 4x19" sections adjustable in depths (gaps of 20mm). Manufactured in steel 1.5 mm.
- Removable side panels with ¼ turn locks.
- Steel rear door with lock.
- ¼ -turn locking ventilated top panels with cable entries.
- 4 adjustable levelling feet.
- Distributed load capacity: 1.000 Kg (static) / 300 Kg (dynamic)
- Finishes: RAL 7016, Dark grey, anthracite (See below for corner options)



RED	U	WIDTH	DEPTH	HEIGHT	DESCRIPTION
CLX126601	12	600mm	600mm	661mm	Glass front door
CLX126611	12	600mm	600mm	661mm	Open front door
CLX186601	18	600mm	600mm	928mm	Glass front door
CLX186611	18	600mm	600mm	928mm	Open front door
CLX246601	24	600mm	600mm	1195mm	Glass front door
CLX246611	24	600mm	600mm	1195mm	Open front door
CLX306601	30	600mm	600mm	1461mm	Glass front door
CLX306611	30	600mm	600mm	1461mm	Open front door
CLX366601	36	600mm	600mm	1728mm	Glass front door
CLX366611	36	600mm	600mm	1728mm	Open front door
CLX366801	36	600mm	800mm	1728mm	Glass front door
CLX366811	36	600mm	800mm	1728mm	Open front door
CLX426601	42	600mm	600mm	1998mm	Glass front door
CLX426611	42	600mm	600mm	1998mm	Open front door
CLX426801	42	600mm	800mm	1998mm	Glass front door
CLX426811	42	600mm	800mm	1998mm	Open front door

WHITE	U	WIDTH	DEPTH	HEIGHT	DESCRIPTION
CLX126604	12	600mm	600mm	661mm	Glass front door
CLX126614	12	600mm	600mm	661mm	Open front door
CLX186604	18	600mm	600mm	928mm	Glass front door
CLX186614	18	600mm	600mm	928mm	Open front door
CLX246604	24	600mm	600mm	1195mm	Glass front door
CLX246614	24	600mm	600mm	1195mm	Open front door
CLX306604	30	600mm	600mm	1461mm	Glass front door
CLX306614	30	600mm	600mm	1461mm	Open front door
CLX366604	36	600mm	600mm	1728mm	Glass front door
CLX366614	36	600mm	600mm	1728mm	Open front door
CLX366804	36	600mm	800mm	1728mm	Glass front door
CLX366814	36	600mm	800mm	1728mm	Open front door
CLX426604	42	600mm	600mm	1998mm	Glass front door
CLX426614	42	600mm	600mm	1998mm	Open front door
CLX426804	42	600mm	800mm	1998mm	Glass front door
CLX426814	42	600mm	800mm	1998mm	Open front door

BLUE	U	WIDTH	DEPTH	HEIGHT	DESCRIPTION
CLX126602	12	600mm	600mm	661mm	Glass front door
CLX126612	12	600mm	600mm	661mm	Open front door
CLX186602	18	600mm	600mm	928mm	Glass front door
CLX186612	18	600mm	600mm	928mm	Open front door
CLX246602	24	600mm	600mm	1195mm	Glass front door
CLX246612	24	600mm	600mm	1195mm	Open front door
CLX306602	30	600mm	600mm	1461mm	Glass front door
CLX306612	30	600mm	600mm	1461mm	Open front door
CLX366602	36	600mm	600mm	1728mm	Glass front door
CLX366612	36	600mm	600mm	1728mm	Open front door
CLX366802	36	600mm	800mm	1728mm	Glass front door
CLX366812	36	600mm	800mm	1728mm	Open front door
CLX426602	42	600mm	600mm	1998mm	Glass front door
CLX426612	42	600mm	600mm	1998mm	Open front door
CLX426802	42	600mm	800mm	1998mm	Glass front door
CLX426812	42	600mm	800mm	1998mm	Open front door


BLACK	U	WIDTH	DEPTH	HEIGHT	DESCRIPTION
CLX126605	12	600mm	600mm	661mm	Glass front door
CLX126615	12	600mm	600mm	661mm	Open front door
CLX186605	18	600mm	600mm	928mm	Glass front door
CLX186615	18	600mm	600mm	928mm	Open front door
CLX246605	24	600mm	600mm	1195mm	Glass front door
CLX246615	24	600mm	600mm	1195mm	Open front door
CLX306605	30	600mm	600mm	1461mm	Glass front door
CLX306615	30	600mm	600mm	1461mm	Open front door
CLX366605	36	600mm	600mm	1728mm	Glass front door
CLX366615	36	600mm	600mm	1728mm	Open front door
CLX366805	36	600mm	800mm	1728mm	Glass front door
CLX366815	36	600mm	800mm	1728mm	Open front door
CLX426605	42	600mm	600mm	1998mm	Glass front door
CLX426615	42	600mm	600mm	1998mm	Open front door
CLX426805	42	600mm	800mm	1998mm	Glass front door
CLX426815	42	600mm	800mm	1998mm	Open front door

ORANGE	U	WIDTH	DEPTH	HEIGHT	DESCRIPTION
CLX126603	12	600mm	600mm	661mm	Glass front door
CLX126613	12	600mm	600mm	661mm	Open front door
CLX186603	18	600mm	600mm	928mm	Glass front door
CLX186613	18	600mm	600mm	928mm	Open front door
CLX246603	24	600mm	600mm	1195mm	Glass front door
CLX246613	24	600mm	600mm	1195mm	Open front door
CLX306603	30	600mm	600mm	1461mm	Glass front door
CLX306613	30	600mm	600mm	1461mm	Open front door
CLX366603	36	600mm	600mm	1728mm	Glass front door
CLX366613	36	600mm	600mm	1728mm	Open front door
CLX366803	36	600mm	800mm	1728mm	Glass front door
CLX366813	36	600mm	800mm	1728mm	Open front door
CLX426603	42	600mm	600mm	1998mm	Glass front door
CLX426613	42	600mm	600mm	1998mm	Open front door
CLX426803	42	600mm	800mm	1998mm	Glass front door
CLX426813	42	600mm	800mm	1998mm	Open front door

• Other corner colours available upon request:



• Standard corner colours:



UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARDS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES



+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.0 Iss 2

