

# Introducing

## Corcom SR Series 20A Power Inlet Connectors


The Corcom SR Series includes a full line of popular AC receptacles. These male and female power line connectors include snap-in and flange mounted models. Now available in 20 Amp versions with flange mount and snap-in configurations. These AC receptacles feature a standard IEC60320-1 inlet for power cords and quick-disconnect terminals for load side connection.



## **KEY FEATURES**

- New 20A Version
- Snap-in and Flange Mounting Options
- Operating Voltage 120/250 VAC
- UL Recognized and CSA Certified for 20A at 125V
- VDE Approved for 16A at 250VAC





#### **STANDARDS AND SPECIFICATIONS**







- UL Recognized
- CSA Certified
- VDE Approved

## **SPECIFICATIONS**

| Rated Current       | 6ESR Models                         | 20ESR Models |  |  |
|---------------------|-------------------------------------|--------------|--|--|
|                     | 15A Max.                            | 20A Max.     |  |  |
| Temperature Rating: | 65°C for "cold" connections         |              |  |  |
| Insulator:          | Thermoplastic UL 94V-0 flame rating |              |  |  |
| Prongs:             | Solid brass, nickel plated          |              |  |  |
| Terminals:          | Brass, tin plated                   |              |  |  |

\*15A versions are VDE approved at 10A, 250VAC. 20A versions are VDE approved at 16A, 250VAC

#### **PRODUCT OFFERING**

| Туре                    | Male Connector Part No. | Female Connector Part No. |  |  |
|-------------------------|-------------------------|---------------------------|--|--|
| PC Pins                 | 6ESRM-P                 | -                         |  |  |
| 15A (max.) Snap-In      | 6ESRMC2                 | 6ESRFC3                   |  |  |
| 15A (max.) Flange Mount | 6ESRM-3                 | 6ESRF-3                   |  |  |
| 20A (max.) Snap-In      | 20ESRMC2                | -                         |  |  |
| 20A (max.) Flange Mount | 20ESRM-3                | -                         |  |  |

#### **CASE DIMENSIONS**


|          | Α     | В                      | С     | D     | E     |
|----------|-------|------------------------|-------|-------|-------|
| Part No. | (max) | +.017 /006<br>+.43 /15 | (max) | (max) | (max) |
| 6ESRM-P  | 1.96  | 1.575                  | 1.094 | 1.118 | .807  |
|          | 49.8  | 40.0                   | 27.8  | 28.39 | 20.5  |
| 6ESRMC2  | 1.182 | -                      | .885  | -     | 1.192 |
|          | 30.0  | -                      | 22.5  | -     | 30.3  |
| 6ESRFC3  | 1.39  | -                      | 1.09  | -     | 1.496 |
|          | 35.5  | -                      | 27.8  | -     | 38.0  |
| 6ESRM-3  | 1.96  | 1.575                  | .885  | 1.19  | 1.275 |
|          | 49.8  | 40.0                   | 22.5  | 30.23 | 32.4  |
| 6ESRF-3  | 1.953 | 1.575                  | 1.133 | -     | 1.496 |
|          | 49.6  | 40.0                   | 28.8  | -     | 38.0  |
| 20ESRMC2 | 1.377 | .921                   | 1.06  | -     | -     |
|          | 35.0  | 23.4                   | 27.0  | -     | -     |
| 20ESRM-3 | 2.087 | 1.653                  | .999  | -     | 1.318 |
|          | 53.0  | 42.0                   | 25.4  | -     | 33.5  |




#### **CASE STYLES**


## **20A Inlets**

#### 20ESRMC2




#### 20ESRM-3







## **15A Inlets**

#### 6ESRM-P





#### 6ESRFC3







#### 6ESRM-3







#### 6ESRMC2








## 6ESRMC2







## FOR MORE INFORMATION

corcom com

#### **TE Technical Support Center**

Internet: te.com/help
USA: +1 (800) 522-6752
Canada: +1 (905) 475-6222
Mexico +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
Germany: +49 (0) 6251-133-1999
UK: +44 (0) 800-267666
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999

Part numbers in this brochure are RoHS Compliant\*, unless marked otherwise.

#### te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved. 8-1773460-7 CIS JG 05/2011

Corcom, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

