

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

87568-1073

Status:

Active

Overview:

Milli-Grid™ Connector System

Description:

Milli-Grid™ Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization Key, with Locking Friction Ramp



Series

image - Reference only

|                               |                                                          |
|-------------------------------|----------------------------------------------------------|
| Documents:                    |                                                          |
| <a href="#">3D Model</a>      | <a href="#">Product Specification PS-87568-004 (PDF)</a> |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>     |

|                                |                                     |
|--------------------------------|-------------------------------------|
| Agency Certification           |                                     |
| CSA                            | LR19980                             |
| UL                             | E29179                              |
| General                        |                                     |
| Product Family                 | IDT and Solder Connectors           |
| Series                         | 87568                               |
| Crimp Quality Equipment        | Yes                                 |
| MolexKits                      | Yes                                 |
| Overview                       | Milli-Grid™ Connector System        |
| Product Name                   | Milli-Grid™                         |
| UPC                            | 822348456376                        |
| Use With                       | 87569-1010 Strain Relief (Optional) |
| Physical                       |                                     |
| Circuits (Loaded)              | 10                                  |
| Circuits (maximum)             | 10                                  |
| Color - Resin                  | Black                               |
| Durability (mating cycles max) | 100                                 |
| Flammability                   | 94V-0                               |
| Gender                         | Female                              |
| Glow-Wire Compliant            | No                                  |
| Lock to Mating Part            | Yes                                 |
| Material - Metal               | Copper Alloy                        |
| Material - Plating Mating      | Gold                                |
| Material - Resin               | Polyester                           |
| Net Weight                     | 0.723/g                             |
| Number of Rows                 | 2                                   |
| Packaging Type                 | Tray                                |
| Panel Mount                    | No                                  |
| Pitch - Mating Interface       | 2.00mm                              |
| Polarized to Mating Part       | Yes                                 |
| Stackable                      | No                                  |
| Temperature Range - Operating  | -20°C to +85°C                      |
| Termination Interface: Style   | IDT or Pierce                       |
| Wire Size AWG                  | 28                                  |
| Electrical                     |                                     |
| Current - Maximum per Contact  | 1A                                  |
| Voltage - Maximum              | 125V                                |
| Material Info                  |                                     |
| Reference - Drawing Numbers    |                                     |
| Product Specification          | PS-87568-004                        |
| Sales Drawing                  | SD-87568-003                        |

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87568Series

Mates With

87831 Vertical PCB Header, 87832 Surface Mount PCB Header, 87833 Right Angle PCB Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description                                 | Product #  |
|---------------------------------------------|------------|
| IDT - Manual - Tool Kit                     | 0621003200 |
| Manual Press with IDT Ribbon Cable Tool Kit | 0621002200 |
| IDT - Manual - Handtool                     | 0621002000 |

This document was generated on 03/23/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**