EAO – Your Expert Partner for **Human Machine Interfaces**

82-6151.1114 - Illuminated pushbutton 16 mm stainless-steel, momentary

82-6151.1114 - Illuminated pushbutton 16 mm stainless-steel, momentary



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

 $\begin{array}{ll} \mbox{Mounting cut-out} & \mbox{\varnothing 19 mm} \\ \mbox{Design} & \mbox{flush} \end{array}$

Front

Front dimension Ø 22 mm
Front shape round
Front ring shape flush

Other Attributes

Operating voltage 24 V AC/DC Weight 0.018 kg
Operation current 10 mA

Operating-/Indication part

Lens optics opaque
Lens material Stainless steel
Lens profile flat
Lens illumination illuminative
Lens colour Stainless steel

IP-Rating

Front protection IP 67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Momentary

Switching element

Switching current 5 A
Contact material Silver
Contacts 1 C

Switching system Snap-action switching element

Switching voltage 250 V AC

Illumination

Illumination Ring with red LED

Function

Illuminated pushbutton


e a o

Stand: 24.04.2014


EAO – Your Expert Partner for **Human Machine Interfaces**

82-6151.1114 - Illuminated pushbutton 16 mm stainless-steel, momentary


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: B = Momentary Contacts: C = Changeover