

### DT-100A Contact Tachometers

**The Series DT-100A Tachometer with micro-processor technology has heralded a superior standard in tachometer accuracy and capabilities for measuring and recording speeds of rotational, linear and surface plus total length.** Offering unprecedented confidence, the DT-100A battery-operated tachometers feature the same rugged, high quality components that have made them the benchmark in the industry. These user-friendly, value-packed units feature memory storage; quick adjustment units knob; length functions; retrieval of last, maximum and minimum values; plus each unit comes standard with a free N.I.S.T. certificate. Units are available with an LCD or vibrant red LED display.

Incorporating the precise technology and user-friendly functions as the DT-100A, the DT-100A-S12 provides an exceptional accuracy in measuring speed and length via its 12" wheel. The larger wheel rotates more slowly than a standard 6" wheel, enabling reliable and safe registration of high speeds.



DT-105A

DT-107A

#### Features

- Outstanding accuracy allows usage in the strictest applications
- Exceptionally rugged die-cast aluminum housing enables usage in the harshest conditions
- Wide field selection of units in both instantaneous rate as well as totalized length satisfies a multitude of user requirements
- Large 5 digit display aids user visibility
- Expansive 10 measurement memory capacity allows quick retrieval of stored data plus additional last, max. & min. values
- Long-life battery (25-40 hrs. continuous use) eliminates concerns of being down during testing
- Compact, ergonomic design allows easy grip
- Rear threaded inserts provides option to mount to stand or other device
- Available display options of either LCD or vibrant, bright red LED
- CE Mark combined with free N.I.S.T. certificate provides peace of mind due to the quality of the instrument



Optional  
DT105A-S12  
with 12"  
Circle Wheel

DT105A  
Shown with  
Included 6"  
Circle Wheel



Standard  
DT-100A in  
Supplied  
Case

## DT-100A Specifications

<b>Display Range</b>	0.10 - 25,000RPM with floating decimal
<b>Accuracy</b>	±0.06 rpm: 0.10 - 999.9 rpm; ±0.6 rpm: 1,000.0 - 9,999.9 rpm; ±0.006% of reading ±1 digit (±2 rpm max.) 25,000 rpm
<b>Display</b>	DT-105A: 5 digit 0.47" (12 mm) high LED; DT-107A: 5 digit 0.4" (10 mm) high LED
<b>Measuring Units</b>	Revolution: RPH, RPM; Feet: FPH, FPM; Miles: MPH; Yards: YPH, YPM; Inches: IPM; Meters: mPH, mPM; Length: m, cm, inches, feet, yards; Total Revolutions: REV
<b>Memory System</b>	13 readings are stored in memory and retained for 5 minutes (last, max., min., and 10 extra measurements)
<b>Detection</b>	Optical coupler, 60 pulses/rev.
<b>Update Time</b>	1 second (typical)
<b>Over Range Indicator</b>	Flashing numerals
<b>Power Requirement</b>	2 AA 1.5V batteries (Life: Approx. DT-105A: 65 hrs.; DT-107A: 40 hrs.)
<b>Operating Temperature</b>	32° - 113°F (0° - 45°C)
<b>Construction</b>	Die-cast aluminum housing
<b>Product Weight</b>	0.9 lb (400 g)
<b>Package Weight</b>	Approx. 2 lb (.91 kg)
<b>Approvals</b>	CE
<b>Dimensions</b>	7.2" L x 2.4" W x 1.8"H (182.5 mm x 60 mm x 46 mm)
<b>Warranty</b>	2-Year
<b>Included Accessories</b>	2 cone adapters, funnel adapter, 3½" extension shaft, carrying case, NIST certificate, master wheel (6" cir.)
<b>Options</b>	-S12 Option: Same as DT-100A except 6" circumference wheel replaced with 12" circumference contact wheel

## Ordering Details

<b>DT-105A</b>	LCD Contact Tachometer with included 6" contact wheel. Includes NIST certificate.
<b>DT-105A-S12</b>	LCD Contact Tachometer with included 12" contact wheel. Includes NIST certificate.
<b>DT-107A</b>	LED Contact Tachometer with laser sensor and contact adapter for use with included 6" contact wheel. Includes NIST certificate.
<b>DT-107A-S12</b>	LED Contact Tachometer with included 12" contact wheel. Includes NIST certificate.

## Accessories

<b>CONE</b>	1/2 inch cone adapter
<b>CONE-3/4</b>	3/4 inch cone adapter
<b>CONE-1-1/4</b>	1-1/4 inch cone adapter
<b>DT-CARRY100</b>	Carrying case for handheld tachometers
<b>EXT-SHAFT</b>	3.5 inch extension shaft for handheld tachometers
<b>FPM-12</b>	12 inch circumference measuring wheel
<b>FPM-6</b>	6 inch circumference measuring wheel
<b>FPM-6-GV</b>	6 inch circumference grooved measuring wheel
<b>FUNNEL</b>	1/2 inch funnel adapter
<b>NIST-TACH</b>	NIST traceable certificate with data

## Included Accessories



DISTRIBUTED BY:

## Optional Accessories



FPM-12 (ft./min) 12" circle



FPM-6-GV (6" circle grooved wheel)

A **Nidec** Group Company  
**SHIMPO**