DESKTOP & INSTRUMENT CASES

UNIVERSAL **ENCLOSURES**

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

SUBRACKS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES

1000 Series Vario Cases


ABS desk cases with inclined aluminium panel, recessed to accept membranes and overlays.

- · Base moulded in high impact ABS
- Aluminium lid mounted by 4x M3 screws
- · Recessed front panel to accept keypad membranes and overlays
- · Polished finish for ease of cleaning
- · Vertical PCB guides in base
- PCB pillars in base
- ABS VL-94 VO material optional



SPECIFICATION	
Protection class	IP54
Standard colours	Front panel grey
	Base grey as standard, white to order
Standard unit includes	Lid & base
	4x M3 machine screws
	4x rubber feet

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT
BIM1005-BLK/PG	BIM1005-GY/PG	97mm	162mm	57mm
BIM1006-BLK/PG	BIM1006-GY/PG	130mm	215mm	72mm




8000 Series Euro Desk Cases

ABS desktop cases with removable base plates for ease of access and flush fitting aluminium front panels.

- · Moulded in high impact ABS
- Aluminium lid mounted by 4x M3 screws
- · Removable base plate for ease of access and fast assembly
- Gloss finish for ease of cleaning
- Integral side PCB slots in enclosure body
- PCB pillars in base

	SPECIFICATION			
	Materials	Body and base plate high impact ABS as standard UL-94 VO ABS to order		
		Panel 1mm thick aluminium		
	Operating temperature	Resistant to temperatures up to 85°C		
	Protection class	IP40		
	Standard colours	Body & base plate grey & black as standard, white to order Aluminium panel grey		
	Standard unit includes	Body & base plate		
		Aluminium panel		
		8/10x M3 fixing screws		
		4x rubber feet		

BLACK	GREY	LENGTH	WIDTH	HEIGHT
BIM8005-BLK/PG	BIM8005-GY/PG	127mm	170mm	70mm
BIM8007-BLK/PG	BIM8007-GY/PG	187mm	243mm	103mm



We operate a constant improvement policy. our products are subject to change without notice