

1

2

3

4

5

CHARACTERISTICS:

MATERIAL:
COLOR: BLACK
STYLE: UL1007


ENVIRONMENTAL
OPERATING TEMPERATURE: -20°C UP TO 80°C
COMPLIANCE: LEAD FREE AND ROHS

WIRE DIMENSION:
AWG: 24

PACKAGING:
10 PCS/BAG

A

Wire end A



Wire end B

B

Wire Length 300mm


Wire end A	62000113722
Wire end B	62000113722

C

RoHS Compliant

G			
F			
E			
D			
C			
B	06-AUG-13	CHARACTERISTIC	QL
A	18-OCT-11	PDF	GG
REV	DATE	FILE	BY

PROJECTION:



GENERAL TOLERANCE

.X = +/- 0.2
.XX = +/- 0.15



APPROVAL: RJ

UNIT: MM

DESCRIPTION: 2.00 MM PRE-CRIMPED CONTACT

SIZE

SCALE:

WERI PART NO: 620120124030

A4

SHEET: 1/2

DRAW: QL

D

1

2

3

4

5

A

B

C

D

Note:
 1.Dimension
 Carton Size:40*30*20(CM)
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15

APPROVAL: RJ

UNIT: MM
 SCALE:
 SHEET: 2/2
 DRAW: QL

DESCRIPTION: WR-WTB 2.00MM PRE-CRIMPED CONTACT
 WERI PART NO: 620 120 124 030

SIZE
A4