


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **503308-1610**  
**Status:** **Active**  
**Overview:** SlimStack™ 0.40mm Pitch Board-to-Board Connectors  
**Description:** 0.40mm Pitch SlimStack™ Board-to-Board, Plug, Surface Mount, Dual Row, Vertical Stacking, 0.70mm Stacking Height, 16 Circuits

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model</a>                                  | <a href="#">Application Specification AS-503304-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                             | <a href="#">Packaging Specification SPK-503308-001 (PDF)</a>  |
| <a href="#">Product Specification PS-503304-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>          |



**General**

|                |   |
|----------------|---|
| Product Family | PCB Headers   |
| Series         | 503308  |
| Application    | Board-to-Board, Signal  |
| Overview       | <a href="#">SlimStack™ 0.40mm Pitch Board-to-Board Connectors</a> |
| Product Name   | SlimStack™  |
| UPC            | 883906714093  |

**Physical**

|                                |                       |
|--------------------------------|-----------------------|
| Breakaway                      | No                    |
| Circuits (Loaded)              | 16                    |
| Circuits (maximum)             | 16                    |
| Color - Resin                  | Black                 |
| Durability (mating cycles max) | 30                    |
| Glow-Wire Compliant            | No                    |
| Mated Height                   | 0.70mm                |
| Material - Metal               | Copper Alloy          |
| Material - Plating Mating      | Gold                  |
| Material - Plating Termination | Gold                  |
| Net Weight                     | 7.192/mg              |
| Number of Rows                 | 2                     |
| Orientation                    | Vertical              |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Packaging Type                 | Embossed Tape on Reel |
| Pitch - Mating Interface       | 0.40mm                |
| Polarized to Mating Part       | No                    |
| Polarized to PCB               | No                    |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40°C to +85°C        |
| Termination Interface: Style   | Surface Mount         |

**Electrical**

|                               |           |
|-------------------------------|-----------|
| Current - Maximum per Contact | 0.3A      |
| Voltage - Maximum             | 50V AC/DC |

**Material Info**

**Reference - Drawing Numbers**

|                           |   |
|---------------------------|---|
| Application Specification | AS-503304-001   |
| Packaging Specification   | SPK-503308-001  |
| Product Specification     | PS-503304-001, RPS-503304-004, RPS-503304-015, RPS-503304-016 |
| Sales Drawing             | SD-503308-001, SD-503308-002                                  |

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

503308Series

**Mates With**

SlimStack™ Board-to-Board Receptacle  
 503304 , 503489

This document was generated on 10/10/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**