

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [21020-0431](#)  
**Status:** **Active**  
**Overview:** Premo-Flex™ FFC and Etched Polyimide Jumpers  
**Description:** 0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 40 Circuits, 0.102m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating  
**Replacement Part Number:** [15266-0431](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-21020-001 \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">21020</a>
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	<u>Premo-Flex™ FFC and Etched Polyimide Jumpers</u>
Product Name	Premo-Flex™ FFC Jumper
Replacement Part Number	<a href="#">15266-0431</a>
UPC	800753140141

**Physical**

Cable Length	0.102m
Circuits (Loaded)	40
Net Weight	1.778/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-21020-001
Sales Drawing	SD-21020-001



*image - Reference only*

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[21020Series](#)

**Use With**

[www.molex.com/product/ffcfpc\\_th.html](http://www.molex.com/product/ffcfpc_th.html)