

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [34912-8041](#)  
**Status:** **Active**  
**Overview:** [Mini50™ Connection Systems](#)  
**Description:** Mini50™ Unsealed, Single Row, Right-Angle Header, 4 Circuit, Polarization Option B, Gray, Tube

**Documents:**

[3D Model](#)  
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	PCB Headers
Series	<a href="#">34912</a>
Application	Power, Signal, Wire-to-Board
Overview	<a href="#">Mini50™ Connection Systems</a>
Product Name	Mini50™
UPC	887191297231

**Physical**

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Polyester Alloy
Net Weight	1.561/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount


**Electrical**

Current - Maximum per Contact	4A
Voltage - Maximum	500V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-34912-001
---------------	--------------



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[34912Series](#)

**Use With**

[560023](#) CTX50 Receptacle Terminal  
 Unsealed