

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [33482-0401](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Sealed Male Connector, Dual Row, 4 Circuits, Polarization A, without Connector Position Assurance, Black

Documents:

[3D Model](#) [Application Specification AS-33472-100 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	33482
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	756054494417

Physical

Circuits (maximum)	4
Circuits Detail	4
Color - Resin	Black, Natural
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	8.181/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	22.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100
Sales Drawing	SD-33482-041



EU RoHS

ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[33482Series](#)

Mates With

[33472](#) Female Dual Row Sealed Connector

Use With

[33000](#) MX150™ Tin (Sn) Male Terminal,
[33011](#) Gold (Au) Male Terminal, [34345-0001](#)
 MX150™ Cavity Plug Sealed