

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [16-02-1116](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: SL™ Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 24-30 AWG, Bag

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#)
[Product Specification PS-71851 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	71851
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-1112 (Reel)
Product Name	SL™
UPC	800753595804
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.060/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info	
Old Part Number	71851-0204

Reference - Drawing Numbers	
Product Specification	PS-70400, PS-71851
Sales Drawing	SD-71851-0204



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71851Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool For SL™ Crimp Terminals	0638258800
Insertion Tool	0011020022
Extraction Tool	0011030036