



Part Number: M85049/47

Right Angle Strain Relief Clamp



Dash Number	Shell Size	Cable Diameter Min - Imperial	Cable Diameter Min - Metric	Cable Diameter Max - Imperial	Cable Diameter Max - Metric
8	8/9	.098	2.5	.234	5.9
10	10/11	.153	3.9	.234	5.9
12	12/13	.190	4.8	.328	8.3
14	14/15	.260	6.6	.457	11.6
16	16/17	.283	7.2	.614	15.6
18	18/19	.325	8.3	.634	16.1
20	20/21	.343	8.7	.698	17.7
22	22/23	.381	9.7	.823	20.9
24	24/25	.418	10.6	.853	21.7

Finish

N = Electroless Nickel

S = 300 Series Steel, Passivated

W = Cadmium, Olive drab over Electroless Nickel