

Data & Signal, Plug, 6.3 mm, 3-pole, solder terminal, shielded



### Description

- Solder terminal:  
for cable mounting
- Data and Signal transfer
- Data and Signal Connectors 3-pole, shielded, straight

### References

Alternative: Housing insulated [4803.1310](#); [4803.1320](#)

### Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

### Technical Data

Diameter	6.3 mm
Number of Poles	3-pole
Ratings DC	2 A / 12 VDC
Ratings AC	2 A / 12 VAC
Dielectric Strength	1000 VDC
Insulation Resistance	> 10000 MΩ @ 500 VDC

Allowable Operation Temp.	-20 °C to 70 °C
Terminal	solder terminal
Housing	screened
Style	straight
Lifetime	10000 Insertions

### Dimensions



### All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/ Sockets	6.3	3-pole	solder terminal	<a href="#">4803.1300</a>

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging unit** 100 Pcs

## Mating Outlets/Connectors

## Category / Description



[Data and Signal Plug/Socket Overview complete](#)

Daten & Signal, Socket, 6.3 mm, 3-pole, solder terminal, shielded	4803.2300
Daten & Signal, Socket, 6.3 mm, 3-pole, solder terminal, insulated	4803.2310
Daten & Signal, Socket, 6.3 mm, 3-pole, solder terminals for PCB, shielded	4803.2320
Daten & Signal, Socket, 6.3 mm, 3-pole, solder terminals for PCB, insulated	4803.2330
Daten & Signal, Inline Socket, 6.3 mm, 3-pole, solder terminal, shielded	4803.3300

[Data and Signal Plug/Socket further types to 4803 UK-Stecker, D=6,5mm](#)