Daten & Signal, Inline Socket, 6.3 mm, 3-pole, solder terminal, shielded





References

Weblinks

Alternative: Housing insulated

Description

- Solder terminal:

- Data and Signal transfer
- Data and Signal Connectors 3-pole, shielded, straight


Technical Data

Diameter	6.3 mm
Number of Poles	3-pole
Ratings DC	2A / 12VDC
Ratings AC	2 A / 12 VAC
Dielectric Strength	1000VDC
Insulation Resistance	> 10000 MΩ @ 500 VDC


pdf-datasheet, html-datasheet, General Product Information, RoHS, CHINA-RoHS, REACH, Mating Connectors, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check

Allowable Operation Temp.	-20°C to 70°C	
Terminal	solder terminal	
Housing	screened	
Style	straight	
Lifetime	10000 Insertions	

Dimensions



Diagrams



4803.3300

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/ Sockets	6.3	3-pole	solder terminal	4803.3300
Most Popular.				
Availability for all produ	ucts can be searched re	eal-time:http://www.schur	ter.com/en/Stock-Check	Stock-Check-SCHURTER

Mating Inlets/Plugs

Category / Description

Data and Signal Plug/Socket Overview complete



Data & Signal, Plug, 6.3 mm, 3-pole, solder terminal, shielded	4803.1300
Data & Signal, Plug, 6.3 mm, 3-pole, solder terminal, insulated	4803.1310
Data & Signal, Plug, 6.3 mm, 3-pole, solder terminal, insulated, angled	4803.1320
Data and Signal Plug/Socket further types to 4803 UK-Stecker, D=6,5mm	



The specifications, descriptions and illustrations indicated in this document are based on current information. All content is subject to modifications and amendments. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability and test each product selected for their own applications.