




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/7/09	D.GRIFFIN
A	ECN 99999: ASSOCIATED MODEL TO DRAWING	8/23/10	D.FRISIELLO
B	ECN 5478: UPDATED PACKAGING NOTE	5/4/11	D. CASTRO
C	ECN 7504: UPDATED ROHS, PACKAGING AND FORMAT	7/9/14	D. CASTRO



USB TYPE A  
MALE





WIRE MAP	
"P1"	"J1"
1	1
2	2
3	3
4	4
SHIELD	SHIELD



**NOTES:**

- ADAPTER SHALL BE 100% TESTED FOR CONTINUITY
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- ADAPTER SHALL BE INDIVIDUALLY PACKAGED USING SUPPLIER BAG AND ADD LABEL LSP-010-3.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)



USB TYPE A  
FEMALE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]  PROJECTION 	APPROVALS		DATE		 <div>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</div>	
	DRAWN BY D. CASTRO		5/5/09			
	CHECKED BY D. PARHAM		5/6/09		CATEGORY	USB
	APPROVED BY S. SMITH		5/6/09			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION  ADAPTER, USB A M/F FLEX/ROTATE				
COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO.  UADFLEX-1	REV. <b>C</b>	
		SCALE: NONE    CAD FILE: UADFLEX-1.SLDRW			SHEET 1 OF 1	