

Y Splitter Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to 2x IEC-320-C13)

MODEL NUMBER: P004-006-2C13



Highlights

- Connect two devices to one power outlet
- UL Listed
- Plug type - C14 to 2 x C13
- 18AWG (0.824mm²), SJT, 10A, 100-250V

Package Includes

- P004-006-2C13 6-ft. AC Power Extension Splitter Cord (C14 to 2 x C13)

Description

Tripp Lite's P004-006-2C13, 6ft Universal AC Power Extension Cord Splitter, allows you to connect two devices with C14 connections, such as computers, to one power outlet. Cuts down on cabling, as well as frees up space on UPS's, Surge Protectors, etc. Main trunk cable measures 47" from C14 plug to the splitter housing, 3" housing, and 22" each on the two C13 legs.

Features

- Power two computers or other device from one outlet
- UL Listed
- Plug type - C14 to 2 x IEC-320-C13 (Device)
- 18AWG (0.824mm²), SJT, 10A, 100-250V
- 6ft overall length - 47" from C14 to split, 22" from split to C13's

Specifications

OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C13 (X2)
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.