

C1 PUSH PULL POWER 3 POLE MALE CONNECTOR  
 CABLE, 3X1.5SQ, NON-SHIELD, BK-Jacket  
 WHITE LABEL


WIRING TABLE

C1	WIRE COLOR	MARKING IN TUBE
3	YELLOW/GREEN	GND
2	BLUE	N
1	BROWN	L

HARTING P/N & REVISION	Cable length(L)
3359 113 100 0004 .00	10000 ± 200

NOTES:

- 1.)CABLE MUST UNDERGO CONTINUITY AND HI-POT(500VDC) TESTING.
- 2.)THE CABLE SHOULD BE PACKED BY THE PLASTIC BAG.  
 THEN PUT IT INTO THE CARTON(THE QTY ACCORDING TO ACTUAL CONDITION)
- 3.)EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT



Contant: POWER IN  
 Front: Arial 1.8 MM  
 WHITE

Connector Marking

DATE CODE & LOT INFORMATION  
 HARTING P/N & REVISION

- 5.)CONNECTOR NEED PRINT WHITE MARKING ACORDING DRAWING.
- 6.)CABLE OPERATION TEMPERATURE: -25°C TO +70°C.
- 7.)OPEN END WIRE NEED USING A WIRING TUBING MARK AS DRAWING.

All rights reserved Department EC PD - CN HARTING Electronics GmbH D-32339 Espelkamp	All Dimensions in mm Original Size DIN A3	Scale 1:1 Free size tol.	Ref. \                 Sub. \
	Created by LIT Inspected by Standardisation Date 2014-10-08 State Checked Out	Title Push-Pull Power, 3 pole, Single-end, L=10M Type TB Number 33591131000004	