

SIDE VIEW

C1  
PUSH PULL POWER 05 POLE FEMALE CONNECTOR


CABLE, 3X2.5SQMM, NON-SHIELD, BK-Jacket

WHITE LABEL

WIRING TABLE

C1	WIRE COLOR	MARKING IN TUBE
5 (GND)	GREEN /YELLOW	GND
4	NC	
3	BLUE	N
2	NC	
1	BROWN	L

HARTING P/N & REVISION	Cable length(L)
3359 113 100 0006 .00	10000 ± 200



Contant: POWER IN  
Front: Arial 1.8 MM  
WHITE

Connector Marking

NOTES:

- 1.)CABLE MUST UNDERGO CONTINUITY AND HI-POT(500VDC) TESTING.
- 2.)THE CABLE SHOULD BE PACKED BY THE PLASTIC BAG. THEN PUT IT INTO THE CARTON(THE QTY ACCORDING TO ACTUAL CONDITION)
- 3.)EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT/

DATE CODE & LOT INFORMATION  
HARTING P/N & REVISION

- 5.)CONNECTOR NEED PRINT WHITE MARKING ACORDING DRAWING.
- 6.)CABLE OPERATION TEMPERATURE: -20°C TO +70°C

All rights reserved Department EC PD - CN HARTING Electronics GmbH D-32339 Espelkamp	All Dimensions in mm Original Size DIN A3	Scale 1:1 Free size tol. \	Ref. \                 Sub. \
	Created by LIT Inspected by Standardisation Date 2014-10-09 State Checked Out	Title Push-Pull Power 5 P fe,Single-end,L=10M Type TB Number 33591131000006	