

D

D

C



C

B

B

A

A



Notes

- 1 SUITABLE HOUSINGS: SERIES HC26
CUSTOMER DRAWING: 1103436, 1103434
- 2 SUITABLE INSERTS: SERIES HC26
CUSTOMER DRAWING: 1103428, 1103429,
1103431, 1103432
- 3 STANDARDS:
DIN EN 61984, DIN EN 60664-1
- 4 CODING GROOVE
- 5 PACKAGING:
40 SETS IN A CARTON, PRE-MOUNTED
- 6 SALEABLE PART
- 7 KIT COMPONENT: FOR INTERNAL USE ONLY

PN 0-1 AS SHOWN

1	1	BULKHEAD HOUSING	ZINC ALLOY	NICKEL PLATED	SERIES HC26, DESIGN METAL	2
1	1	SEALING	FKM	GREY	SERIES HC26, BULKHEAD HSG	1
-2	-1	DESCRIPTION	MATERIAL	SURFACE/COLOR	NOTE	ITEM
PN/QTY		PARTS LIST				

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:
MASSEINHEITEN:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES/WINKEL ±1°
FINISH/OBERFLAECHE/FARBE
-

DWN
T.VETTER 23JAN2009

CHK
H.BRAUN 26JAN2009

APVD
T.SCHNURPFIL 26JAN2009

PRODUCT SPEC
PRODUKTSPEZ.
108-74097

APPLICATION SPEC
VERARBEITUNGSSPEZ.
114-74103

WEIGHT
GEWICHT
-

NAME
BULKHEAD HOUSING ASS'Y
SERIES HC26, DESIGN METAL
POWER 4 NET

SIZE
A3

CAGE CODE
00779

DRAWING NO.
ZEICHNUNGS-NR.
C=1103436

RESTRICTED TO
NUR FUER
-

CUSTOMER DRAWING

/KUNDENZEICHNUNG

SCALE
MASSSTAB
2:1

SHEET
BLATT
1 OF
VON 1

REV
D2