

ToLEDo Outdoor Ball

Ball IP44 Red B22

0026882

Range features



PRODUCT OVERVIEW

Light colour	
Technology	LED
Ordering number	0026882
Average life (Rated) (h)	25000
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	B22
Type	ToLEDo Outdoor Ball
EAN code	54 10288268828
CRI (Ra)	
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Efficacy (Rated) (lm/w)	
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Colour	

ToLEDo Outdoor Ball

Ball IP44 Red B22

0026882

DATA TABLE

General data

Ordering number	0026882
Technology	LED
Dry applications use only	No
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000
Energy saving lamp	Yes
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	B22
Type	ToLEDo Outdoor Ball
EAN code	5410288268828
E-number SE	8296502
Product name	Ball IP44 Red B22
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Fixture rating	Open
Intended purpose	No
No. of switching cycles before premature failure (min)	100000
Special purpose lamp	Yes
Transformer required	No
Sales pack quantity	1
Optimal operating condition (°C)	25

Optical data

Light colour	
CRI (Ra)	
Suitable for accent lighting	No
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Luminous flux (Nominal) (lm)	
Lumen maintenance at end of nominal life (%)	70
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

ToLEDo Outdoor Ball

Ball IP44 Red B22

0026882

Electrical data

kWh per 1000 hours burning time	1
Efficacy (Rated) (lm/w)	
Watt (Rated) (W)	0.5
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Current (A)	20
Lamp power factor	0.15

Physical data

Weight (kg)	0.02
Colour	
Length base to pin Min-Max - B	67
Lamp Length (mm) - C/L	67
Max. Lamp Diameter (mm) - D	45
Lamp dimension equal to filament lamp equivalent	Yes
Diameter (mm)	45
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	8.50 x 4.40 x 4.40
Inner package dimensions (L x W x H) (cm)	22.50 x 9.20 x 9.50
Inner package net weight (kg)	0.23
Outer package dimensions (L x W x H) (cm)	49.50 x 29.50 x 11.50

ToLEDo Outdoor Ball

Ball IP44 Red B22

0026882

TECHNICAL DRAWINGS

