

# ToLEDo Outdoor Ball

Ball IP44 Blue E27

**0026885**

## Range features



## PRODUCT OVERVIEW

Light colour	
Technology	LED
Ordering number	0026885
Average life (Rated) (h)	25000
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	E27
Type	ToLEDo Outdoor Ball
EAN code	5410288268859
CRI (Ra)	
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Efficacy (Rated) (lm/w)	
Watt (Nominal) (W)	0.5
Voltage (V)	220-240
Colour	

# ToLEDo Outdoor Ball

Ball IP44 Blue E27

**0026885**

## DATA TABLE

### General data

Ordering number	0026885
Technology	LED
Dry applications use only	No
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000
Energy saving lamp	Yes
Lamp finish	Coloured
Lamp shape	Ball
Dimmable	No
Cap/Base	E27
Type	ToLEDo Outdoor Ball
EAN code	5410288268859
E-number SE	8296506
Product name	Ball IP44 Blue E27
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Fixture rating	Open
Intended purpose	No
No. of switching cycles before premature failure (min)	100000
Special purpose lamp	Yes
Transformer required	No
Sales pack quantity	1
Optimal operating condition (°C)	25

### Optical data

Light colour	
CRI (Ra)	
Suitable for accent lighting	No
Colour temperature (K)	
Luminous flux (Rated) (lm)	
Luminous flux (Nominal) (lm)	
Lumen maintenance at end of nominal life (%)	70
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

## ToLEDo Outdoor Ball

Ball IP44 Blue E27

**0026885**

### Electrical data

<b>kWh per 1000 hours burning time</b>	1
<b>Efficacy (Rated) (lm/w)</b>	
<b>Watt (Rated) (W)</b>	0.5
<b>Watt (Nominal) (W)</b>	0.5
<b>Voltage (V)</b>	220-240
<b>Current (A)</b>	20
<b>Lamp power factor</b>	0.15

### Physical data

<b>Weight (kg)</b>	0.02
<b>Colour</b>	
<b>Length base to pin Min-Max - B</b>	70
<b>Lamp Length (mm) - C/L</b>	70
<b>Max. Lamp Diameter (mm) - D</b>	45
<b>Lamp dimension equal to filament lamp equivalent</b>	Yes
<b>Diameter (mm)</b>	45
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	8.50 x 4.40 x 4.40
<b>Inner package dimensions (L x W x H) (cm)</b>	22.50 x 9.20 x 9.50
<b>Inner package net weight (kg)</b>	0.23
<b>Outer package dimensions (L x W x H) (cm)</b>	49.50 x 29.50 x 11.50

## ToLEDo Outdoor Ball

Ball IP44 Blue E27

**0026885**

### TECHNICAL DRAWINGS

---

