

				Ц
	(
This document is the property of and embodies CONFIDENTIAL and	ROPRIETARY information of FCI. No part of the information shown	on this document may be used in any way or disclosed to others	ij	<u>C</u>
This document is the property o	PROPRIETARY information of FCI.	on this document may be used ii	without the written consent of FCI.	Copyright FCI.
	(

- MINI PV TERMINAL WITH 22-36 GAUGE WIRE
- 6. Rohs Compliant Product Specifications:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.





mat′	mat´l. code				surface / tolera			ance		projection		produc	t fai	mily									
	10036738			ISO 13	60 1302			06 ISO 1101				BERGCON											
ltr	ecn no) (dr	date		tolerano	wise specified				7 5	J	title										
K	V07-05	533 H	НТВ	07.08	3.21	angle				±C).3	mm			1 MINI LATCH								
L	B-143	321 L	_MU	13.03	.21	angte	linear		.XX	±C).13			-							-		
								.XXX	X ±0.05		scale	2 5	:1	HOUSING SR POLARIZED									
						dr			N	13.0	3.21				dwg no	O			S	heet	1 0	f 1	size
						engr			N 13.0		3.21			. Ī.				78211 A				^ -	
						chr J.COMPAGNON		GNON 13.03.21								/ 0.	Z				Аз		
	appd LMU		13.0	3.21				type CUSTOMER Drawin							ing								
shee	et n	evisio	חכ																				
inde:	X S	heet																					
	4 5												6										

PDS: Rev :L

2 | 1 |

STATUS:Released

Printed: Oct 02, 2013