

HYDRAULIC TOOLING SPREADSHEET

PRODUCT FAMILY	WIRE SIZE	Wire Class	CONTACT	REDUCING BUSHING	HYDRAULIC TOOL					HYDRAULIC BATTERY		NUMBER OF CRIMPS	REELED CONTACT	INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS	
					TOOL DIE LESS 4 INDENT	NUMBER OF CRIMPS	TOOL CHANGEABLE DIES REQ'D	NUMBER OF CRIMPS	DIE	TOOL CHANGEABLE DIES REQ'D	DIE					
Pin & Socket 10 Amp PP10	14-16 AWG	N/A	1203G1 (PIN) 263G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	263G1	1S6373	N/A	
	14-16 AWG	N/A	1202G1 (SOCKET) 264G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	264G1	1S6373	N/A	
Pin & Socket 30 Amp PP30	10-14 AWG	N/A	113919P1/ 1230G1 113920P1/ 1232G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6345	1S6344	
	16-20 AWG	N/A	1332	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
PP15	14-16 AWG	N/A	261G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	14-16 AWG	N/A	261G1-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	12-16 AWG	N/A	1331	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
PP15	16-20 AWG	N/A	262G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
	16-20 AWG	N/A	262G1-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	12-16 AWG	N/A	261G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6378	N/A	
	12-16 AWG	N/A	261G1-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP45	10-14 AWG	N/A	261G2	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
	10-12 AWG	N/A	261G2-LP1K	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	14 AWG	N/A	261G2-LP1K	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	10-12 AWG	N/A	261G2-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	14 AWG	N/A	261G2-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	10-12 AWG	N/A	261G2-LPBKSP	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	14 AWG	N/A	261G2-LPBKSP	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP30	12-16 AWG	N/A	269G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP45	10-14 AWG	N/A	269G3	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP15	16-20 AWG	N/A	269G2	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP30	12-16 AWG	N/A	269G1-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP45	10-12 AWG	N/A	269G3-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	14 AWG	N/A	269G3-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP15	16-20 AWG	N/A	269G2-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP45 Super-Flex	6mm, #10-14 AWG Low Det	N/A	200G1L	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	6mm, #10-14 AWG Low Det	N/A	200G1L-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#16-20 AWG Low Det	N/A	200G2L	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#16-20 AWG Low Det	N/A	200G2L-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#10-14 AWG High Det	N/A	201G1H	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#10-14 AWG High Det	N/A	201G1H-LPBK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#16-20 AWG High Det	N/A	201G2H	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP75/SB50 W/O BUSHINGS	#6 AWG High Det	N/A	5900	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072 / 1S1030A	
	#6 AWG Low Det	N/A	1307	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#8 AWG	N/A	5952	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#10-12 AWG	N/A	5915	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	Thin Wall #10	N/A	5914	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 low detent Ni Pl	N/A	1C0608P32	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#10-12 low detent Ni Pl	N/A	1C0608P33	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 low detent	N/A	1C0608P36	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP75/SB50 W/ BUSHINGS	#8 AWG	N/A	5900	5912	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072 / 1S1030A	
	#10-12 AWG	N/A	5900	5910	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#14-16 AWG	N/A	5900	5913	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SB550/ SBO60/ SBE 80	16mm SBE80/SBO60	N/A	1339G1-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6367 / 1S6363	1S6330/1S6331	
	16mm SB550	N/A	1339G2	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
		N/A	1339G2-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#10/12 SB550	N/A	1339G3	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6417	
		N/A	1339G3-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	25mm SBE/O	N/A	1339G4	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
		N/A	1339G4-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#8 SBS 50	N/A	1339G5	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
		N/A	1339G5-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	W/ BUSHINGS	#6-8 AWG	N/A	1339G2	5912	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		#6-10/12AWG	N/A	1339G2	5910	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
#6-14/16AWG		N/A	1339G2	5913	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
		N/A														

HYDRAULIC TOOLING SPREADSHEET

PRODUCT FAMILY	WIRE SIZE	Wire Class	CONTACT	REDUCING BUSHING	HYDRAULIC TOOL					HYDRAULIC BATTERY		NUMBER OF CRIMPS	REELED CONTACT	INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS	
					TOOL DIE LESS 4 INDENT	NUMBER OF CRIMPS	TOOL CHANGEABLE DIES REQ'D	NUMBER OF CRIMPS	DIE	TOOL CHANGEABLE DIES REQ'D	DIE					
PP120 W/O BUSHINGS	#2 AWG	N/A	1319	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
	#4 AWG	N/A	1319G4	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG	N/A	1319G6	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SB120	#2 AWG	N/A	6811G1	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1030A	
	#4 AWG	N/A	6811G2	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG	N/A	6811G3	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG low det	N/A	6811G4	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG low det	N/A	6811G4-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#4 AWG low det	N/A	6811G5	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#4 AWG low det	N/A	6811G5-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#2 AWG low det	N/A	6811G6	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#2 AWG low det	N/A	6811G6-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP120 W/ BUSHINGS	#4 AWG	N/A	1319	5919	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072	
	#6 AWG	N/A	1319	5920	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#8 AWG	N/A	1319	5921	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
PP180/SB175 W/O BUSHINGS	1/O	N/A	1382	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072 / 1S1030A	
	#2 AWG	N/A	1383	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#4 AWG	N/A	1384	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#1 AWG	N/A	1347	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#1 AWG	N/A	1347-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG	N/A	1348	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	#6 AWG	N/A	1348-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	W/ BUSHINGS	#1 AWG	N/A	1382	5687	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1072 / 1S1030A
		#2 AWG	N/A	1382	5690	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
#4 AWG		N/A	1382	5693	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
#6 AWG		N/A	1382	5663	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
#10 AWG		N/A	1382	5648	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SB350 W/O BUSHINGS	300 MCM	N/A	910	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1030A	
	4/O	N/A	908	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	3/O	N/A	916	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	2/O	N/A	907	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	1/O	N/A	917	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	1/O	N/A	907	5918	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S1030A	
SB060/SBE80/SBE/ X160/175/320/350 W/O bushings	1/O	N/A	6384G1	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6330/S6331/S6217/1S1094	
	1/O	N/A	6384G1-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	35 mm²	N/A	6384G2	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	35 mm²	N/A	6394	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	35 mm²	N/A	6394-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	1/O (finger safe)	N/A	6393G1	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	1/O (finger safe)	N/A	6393G1-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	1/O (finger safe)	N/A	6394W	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	W/ Bushing	#1 AWG	N/A	6384G1	5687	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		#2 AWG	N/A	6384G1	5690	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		#4 AWG	N/A	6384G1	5693	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		#6 AWG	N/A	6384G1	5663	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
#10 AWG		N/A	6384G1	5648	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
16 mm²		N/A	6384G2	5920	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SB060/SBE80/SBE/X160/175/320/350	2/O	N/A	6354	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6330/S6331/S6217/1S1094	
	2/O	N/A	6354-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	3/O	N/A	6355	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	3/O	N/A	6355-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	4/O	N/A	6356	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	4/O	N/A	6356-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	300MCM	N/A	6358	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	300MCM	N/A	6358-BK	N/A	1368	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	W/ Bushing	1/O	N/A	6354	5918	N/A	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		1/O	N/A	6354	5918	N/A	Dbl	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
SBE/SBX320/350	50mm	N/A	1341G1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6217/1S1094	
	50mm	N/A	1341G1-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	70mm	N/A	1341G2	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	70mm	N/A	1341G2-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	95mm	N/A	1341G3	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	95mm	N/A	1341G3-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
	95mm	N/A	1341G3-BK	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SB0 320 GROUND PIN	#4 AWG	N/A	2-8352P1	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
SBE 700	250MCM x 2 / 4/O x2	N/A	6170G1	N/A	N/A	N/A	Burdy Y750	N/A	N/A	N/A	N/A	N/A	N/A	N/A	1S6407	

HYDRAULIC TOOLING SPREADSHEET

PRODUCT FAMILY	WIRE SIZE	Wire Class	CONTACT	REDUCING BUSHING	HYDRAULIC TOOL					HYDRAULIC BATTERY		NUMBER OF CRIMPS	REELED CONTACT	INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS	
					TOOL DIE LESS 4 INDENT	NUMBER OF CRIMPS	TOOL CHANGEABLE DIES REQ'D	NUMBER OF CRIMPS	DIE	TOOL CHANGEABLE DIES REQ'D	DIE					
EBC 80, 160, 320	#8 AWG	K	80-1010	N/A	N/A	N/A	1387G3	Dbl	1322G16(MK6-50)	1370	1322G16(MK6-50)	Dbl	N/A	N/A	N/A	
	#8 AWG	M	80-1010	N/A	N/A	N/A	1387G3	Dbl	1322G16(MK6-50)	1370	1322G16(MK6-50)	Dbl	N/A	N/A	N/A	
	#8 AWG	M	80-1110	N/A	N/A	N/A	1387G3	Dbl	1322G16(MK6-50)	1370	1322G16(MK6-50)	Dbl	N/A	N/A	N/A	
	10mm	N/A	80-1010	N/A	N/A	N/A	1387G3	Dbl	1322G16(MK6-50)	1370	1322G16(MK6-50)	Dbl	N/A	N/A	N/A	
	10mm	N/A	80-1110	N/A	N/A	N/A	1387G3	Dbl	1322G16(MK6-50)	1370	1322G16(MK6-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	K	80-1016	N/A	N/A	N/A	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	M	80-1016	N/A	N/A	N/A	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	M	80-1116	N/A	N/A	N/A	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	16mm	N/A	80-1016	N/A	N/A	N/A	1387G3	Dbl	1322G10(MK8-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	16mm	N/A	80-1116	N/A	N/A	N/A	1387G3	Dbl	1322G10(MK8-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	25mm	N/A	80-1025	N/A	N/A	N/A	1387G3	Dbl	1322G15(ME9-50)	1370	1322G15(ME9-50)	Dbl	N/A	N/A	N/A	
	25mm	N/A	80-1125	N/A	N/A	N/A	1387G3	Dbl	1322G15(ME9-50)	1370	1322G15(ME9-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	K	160-1016	N/A	1368	Sngl	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	M	160-1016	N/A	1368	Sngl	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	#6 AWG	M	160-1116	N/A	1368	Sngl	1387G3	Dbl	1322G9 (ME3-50)	1370	1322G9 (ME3-50)	Dbl	N/A	N/A	N/A	
	#4 AWG	K	160-1025	N/A	1368	Sngl	1387G3	Dbl	1322G12 (M83-50)	1370	1322G12 (M83-50)	Dbl	N/A	N/A	N/A	
	#4 AWG	M	160-1025	N/A	1368	Sngl	1387G3	Dbl	1322G12 (M83-50)	1370	1322G12 (M83-50)	Dbl	N/A	N/A	N/A	
	#4 AWG	M	160-1125	N/A	1368	Sngl	1387G3	Dbl	1322G12 (M83-50)	1370	1322G12 (M83-50)	Dbl	N/A	N/A	N/A	
	#2 AWG	K	160-1035	N/A	1368	Sngl	1387G3	Dbl	1322G7 (MK12-50)	1370	1322G7 (MK12-50)	Dbl	N/A	N/A	N/A	
	#2 AWG	M	160-1035	N/A	1368	Sngl	1387G3	Dbl	1322G7 (MK12-50)	1370	1322G7 (MK12-50)	Dbl	N/A	N/A	N/A	
	#2 AWG	M	160-1135	N/A	1368	Sngl	1387G3	Dbl	1322G7 (MK12-50)	1370	1322G7 (MK12-50)	Dbl	N/A	N/A	N/A	
	1/0	K	160-1050	N/A	1368	Sngl	1387G3(Cembre)	Dbl	1322G4 (ME14-50)	1370	1322G4 (ME14-50)	Dbl	N/A	N/A	N/A	
	1/0	M	160-1050	N/A	1368	Sngl	1387G3(Cembre)	Dbl	1322G4 (ME14-50)	1370	1322G4 (ME14-50)	Dbl	N/A	N/A	N/A	
	1/0	M	160-1150	N/A	1368	Sngl	1387G3(Cembre)	Dbl	1322G4 (ME14-50)	1370	1322G4 (ME14-50)	Dbl	N/A	N/A	N/A	
	1/0	K	320-1050	N/A	N/A	N/A	N/A									
	1/0	M	320-1050	N/A	N/A	N/A	1387G3(Cembre)	Dbl	1322G4 (ME14-50)	1370	1322G4 (ME14-50)	Dbl	N/A	N/A	N/A	
	1/0	M	320-1150	N/A	N/A	N/A	1387G3(Cembre)	Dbl	1322G4 (ME14-50)	1370	1322G4 (ME14-50)	Dbl	N/A	N/A	N/A	
	2/0	K	320-1070	N/A	N/A	N/A	1387G3(Cembre)	Dbl	1322G3 (ME17-50)	1370	1322G3 (ME17-50)	Dbl	N/A	N/A	N/A	
	2/0	M	320-1070	N/A	N/A	N/A	1387G3(Cembre)	Dbl	1322G2 (ME19-50)	1370	1322G2 (ME19-50)	Dbl	N/A	N/A	N/A	
	2/0	M	320-1170	N/A	N/A	N/A	1387G3(Cembre)	Dbl	1322G2 (ME19-50)	1370	1322G2 (ME19-50)	Dbl	N/A	N/A	N/A	
	3/0	K	320-1095	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	3/0	M	320-1095	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	3/0	M	320-1195	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	95mm-4/0	K	320-1095	N/A												
	95mm-4/0	M	320-1095	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	156395,6,7,8,9,156400
	95mm-4/0	M	320-1195	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	4/0	K	320-1004	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	4/0	M	320-1004	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	4/0	M	320-1104	N/A	1368	Dbl	1387G3(Cembre)	Dbl	1322G1 (ME24-50)	1370	1322G1 (ME24-50)	Dbl	N/A	N/A	N/A	
	EBC Auxiliary Contacts	14 AWG	N/A	80-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		16 AWG	N/A	80-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		18 AWG	N/A	80-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		14 AWG	N/A	80-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		16 AWG	N/A	80-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
		18 AWG	N/A	80-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
8 AWG		N/A	160-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
10 AWG		N/A	160-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-12	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-13	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
10 AWG		N/A	160-14	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
12 AWG		N/A	160-14	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-14	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
10 AWG		N/A	160-15	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
12 AWG		N/A	160-15	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
			160-15	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-18,2-18,1-16,1-14		N/A	320-22	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-18,2-18		N/A	320-23	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-16,1-14		N/A	320-23	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-18,2-18		N/A	320-24	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-16,1-14		N/A	320-24	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	
1-18,2-18,1-16,1-14		N/A	320-25	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	

HYDRAULIC TOOLING SPREADSHEET

PRODUCT FAMILY	WIRE SIZE	Wire Class	CONTACT	REDUCING BUSHING	HYDRAULIC TOOL					HYDRAULIC BATTERY		NUMBER OF CRIMPS	REELED CONTACT	INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS	
					TOOL DIE LESS 4 INDENT	NUMBER OF CRIMPS	TOOL CHANGEABLE DIES REQ'D	NUMBER OF CRIMPS	DIE	TOOL CHANGEABLE DIES REQ'D	DIE					
PMHP A Series	#6 AWG	K & M	PMHPAP05	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G9	B50GA (1370)	1322G9	Dbl	N/A	N/A	N/A	
	16 mm	5	PMHPAP04	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G10	B50GA (1370)	1322G10	Dbl	N/A	N/A	N/A	
	#4 AWG	K & M	PMHPAP03	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G8	B50GA (1370)	1322G8	Dbl	N/A	N/A	N/A	
	25 mm	5	PMHPAP02	N/A	1368	Sngl	HT51 (1387G3)	Dbl	1322G11	B50GA (1370)	1322G11	Dbl	N/A	N/A	N/A	
	#2 AWG	K & M	PMHPAP01	N/A	1368	Sngl	HT51 (1387G3)	Dbl	1322G7	B50GA (1370)	1322G7	Dbl	N/A	N/A	N/A	
	35 mm	5	PMHPAP01	N/A												
	#6 AWG	K & M	PMHPAS05	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G9	B50GA (1370)	1322G9	Dbl	N/A	N/A	N/A	
	16 mm	5	PMHPAS04	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G10	B50GA (1370)	1322G10	Dbl	N/A	N/A	N/A	
	#4 AWG	K & M	PMHPAS03	N/A	N/A	Sngl	HT51 (1387G3)	Dbl	1322G8	B50GA (1370)	1322G8	Dbl	N/A	N/A	N/A	
	25 mm	5	PMHPAS02	N/A	1368	Sngl	HT51 (1387G3)	Dbl	1322G11	B50GA (1370)	1322G11	Dbl	N/A	N/A	N/A	
	#2 AWG	K & M	PMHPAS01	N/A	1368	Sngl	HT51 (1387G3)	Dbl	1322G7	B50GA (1370)	1322G7	Dbl	N/A	N/A	N/A	
	35 mm	5	PMHPAS01	N/A												
	PMHP B Series	1/0 AWG	K & M	PMHPBP04	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G13	B50GA (1370)	1322G13	Dbl	N/A	N/A	N/A
		1/0 mm	K & M	PMHPBS04	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G13	B50GA (1370)	1322G13	Dbl	N/A	N/A	N/A
		1/0 AWG	K & M	PMHPBS09	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G13	B50GA (1370)	1322G13	Dbl	N/A	N/A	N/A
50 mm		5	PMHPBP04	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G13	B50GA (1370)	1322G13	Dbl	N/A	N/A	N/A	
50 mm		5	PMHPBS04	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G13	B50GA (1370)	1322G13	Dbl	N/A	N/A	N/A	
2/0		K & M	PMHPBP03	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
2/0		K & M	PMHPBP03	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
2/0		K & M	PMHPBS08	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
70 mm		5	PMHPBP03	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
70 mm		5	PMHPBS03	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
70 mm		5	PMHPBS08	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G3	B50GA (1370)	1322G3	Dbl	N/A	N/A	N/A	
95 mm		5	PMHPBP02	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G1	B50GA (1370)	1322G1	Dbl	N/A	N/A	N/A	
95 mm		5	PMHPBS02	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G1	B50GA (1370)	1322G1	Dbl	N/A	N/A	N/A	
95 mm		5	PMHPBS07	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G1	B50GA (1370)	1322G1	Dbl	N/A	N/A	N/A	
4/0 AWG		K & M	PMHPBP01	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G14	B50GA (1370)	1322G14	Dbl	N/A	N/A	N/A	
4/0 AWG		K & M	PMHPBS01	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G14	B50GA (1370)	1322G14	Dbl	N/A	N/A	N/A	
4/0 AWG		K & M	PMHPBS06	N/A	1368	Dbl	HT51 (1387G3)	Dbl	1322G14	B50GA (1370)	1322G14	Dbl	N/A	N/A	N/A	
Power Mod		#12 AWG	N/A	PM16p12S30	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	TS6420
Power Drawer	#12 AWG	N/A	PC12SSN	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	TS6416	