Catamount®



NOTES:

1. FLAMABILITY: UL94HB
2. OPERATING TEMPERATURE: 185°F [85°C] MAX.
3. MINIMUM TENSILE RATING: 30 LBS [133 N]

CATALOG NUMBER	WIRE BUNDLE (MAX.)	MATERIAL	COLOR	L
TT-7-30-0-L	1.750 [44,45]	NYLON 6.6, WEATHERABLE	BLACK	7.737 [196,51]
TT-7-30-9-L		NYLON 6.6	NATURAL	
TT-11-30-0-L	3.000 [76,2]	NYLON 6.6, WEATHERABLE	BLACK	11.747 [298,37]
TT-11-30-9-L		NYLON 6.6	NATURAL	
TT-14-30-0-L	4.000 [101,6]	NYLON 6.6, WEATHERABLE	BLACK	14.737 [374,24]
TT-14-30-9-L		NYLON 6.6	NATURAL	

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.

REVISIONS

- SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****

Thomas&Betts
www.tnb.com

DESCRIPTION: **TWIST TAIL CABLE TIE**

ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
FD55631 / (2011218)	1 OF 1	-	WSD-000536

THIS DRAWING IS INTENDED FOR DESCRIPTIVE PURPOSES ONLY. AND THE RIGHT IS RESERVED TO DEVIATE FROM ANY OF THE DETAILS SHOWN HEREON.
©2009 Thomas & Betts - Proprietary, All Rights Reserved