

## Black Box Products

### Cables > Computer & Data Cables

#### Extended-Distance Data Cable, Office Environment, PVC Jacket, 12 Conductors (6 Pairs), 1000-ft. (304.8-m)

Send RS-232 data up to 500 feet in your office environment.

EDN12A-1000

##### **Product Highlights**

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!



<b>Cable Type</b>	Twisted pair, PVC jacket
<b>Capacitance</b>	12 pF/ft. $\pm$ 2 pF/ft.
<b>Conductor Gauge</b>	24 AWG (7 x 32 AWG) stranded
<b>Resistance</b>	25 ohms/1000 ft.
<b>Shield</b>	Foil wrap with drain wire

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight. For shipping weight, please contact Black Box customer service at 1-800-316-7107.