

13U SmartRack 4-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST13



Highlights

- 13U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST13
- Installation hardware
- 16x M6 cagenuts, screws, washers
- Cable management hooks
- Owner's manual with warranty information

Description

SmartRack 4-post open frame racks are ideal for cost conscious 19 inch rack mount applications. Multiple units can be bolted together side by side.

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 39 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	4-Post
PHYSICAL	



Installed Whole System Maximum Rack Depth (in.)	39.3
Installed Whole System Maximum Rack Depth (cm)	99.82
Installed Whole System Minimum Rack Depth (in.)	22
Installed Whole System Minimum Rack Depth (cm)	55.88
Rack Height (U Spaces)	13
Shipping Dimensions (hwd / in.)	4.13 x 5.71 x 43.3
Shipping Dimensions (hwd / cm)	10.5 x 14.5 x 109.98
Shipping Weight (lbs.)	40
Shipping Weight (kg)	18
Unit Dimensions (hwd / in.)	28 x 20.20 x 22-39
Unit Dimensions (hwd / cm)	71.12 x 51.3 x 55.9~99.06 (depth adjustable)
Unit Weight (lbs.)	39
Unit Weight (kg)	17.55
Unit Dimensions (cm)	71.12 x 51.31 x 55.88~99.1 (depth adjustable)
Color	Black
Weight Capacity - Stationary (lbs.)	1000
Weight Capacity - Stationary (kg)	453.6
Hinged (Swings Away from Wall Bracket)	No
SPECIAL FEATURES	
Grounding Lug	Includes nuts, bolts, and washers to attach to user-supplied ground wire
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty