

Power It! 9-Outlet Power Strip, 15-ft. Cord

MODEL NUMBER: TLM915NC



Description

Tripp Lite's Power It! TLM915NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 9 NEMA 5-15R outlets (including one end-mounted outlet ideal for accommodating a transformer without blocking other outlets), 15-foot AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 9 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 9 NEMA 5-15R outlets - including one end mounted outlet ideal for accommodating a transformer without blocking other outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-foot AC power cord
- Rugged metal case provides extra safety and durability
- UL certification
- Includes an end-mounted outlet ideal for accommodating a transformer without blocking other outlets

Highlights

- 9 outlets (including 1 end-mounted outlet)
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15 ft. power cord
- Rugged metal case
- Keyhole mounting slots

Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

Package Includes

- TLM915NC power strip
- Warranty information
- Instruction manual



Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(9) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	End-mounted outlet is ideal for accommodating a transformer without blocking other outlets
Outlet Orientation	Single row of 8 plus 1 end-mounted outlet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.5
Input Cord Gauge Type	SJT 14AWG
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Shipping Dimensions (hwd / in.)	15.5 x 6.5 x 2.25
Shipping Dimensions (hwd / cm)	39.4 x 16.5 x 5.7
Shipping Weight (lbs.)	3
Shipping Weight (kg)	1.4
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 2
Unit Dimensions (hwd / cm)	35 x 6.35 x 5.1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	2.8
Unit Weight (kg)	1.3
Material of Construction	Metal case
Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	27.4mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 203.2mm; Distance between end tabs = 330.17mm
CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.