

USB 2.0 Hi-Speed Active Extension Repeater Cable (A M/F), 10M (33-ft.)

MODEL NUMBER: **U026-10M**



Description

Tripp Lite's 10-meter (33 ft.) USB 2.0 active extension cable is a bus powered extension cable that can be used to increase the length of a device cable without the worry of signal loss and potential performance problems.

USB limits a cable's length to 16ft. Any length above 16 feet requires the use of an active cable such as this one. This cable has a signal booster built in. The overall cable length can be extended up to 131ft by daisy chaining up to 4 of these active cables. The cable must be plugged directly into a USB port (either on the PC or a hub).

Use a standard 6' 10' or 15' USB A-B cable to reach the desired distance. The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-004-R](#)) that is connected to the U026-10M.

Features

- 10 meter (33 ft.) USB2.0 Active Extension Cable, USB-A Male to USB-A Female
- Full 480Mbps Transfer rate, as well as backward compatible to USB 1.1 (12Mbps)
- Daisy Chain four cables for a total of 40 Meters (131ft)
- Bus Powered...no external power required
- Compatible with all major operating systems...Plug-and-Play; no software to load
- The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-004-R](#)) that is connected to the U026-10M.

Highlights

- Extends and Boosts the signal to any USB device
- Supports data transfer speeds up to 480Mbps
- Built in Repeater maintains Hi-Speed USB signal quality, and electrical / timing specifications
- Plug and Play....Compatible with all major operating systems

System Requirements

- USB 2.0 enabled computer (Windows or MAC)
- The U026-10M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-004-R](#)) that is connected to the U026-10M.

Package Includes

- 10-Meter (33 ft.) USB2.0 A/A Hi-Speed Active Extension / Repeater Cable

Specifications

General Info	
RoHS	Y



OVERVIEW	
Chromebook Compatible	Yes
Style	USB
Model Type	Connectivity
Cable Types	USB
OUTPUT	
USB Charging	No
INPUT	
Cable Length (ft.)	33
Cable Length (m)	10
PHYSICAL	
Color	Gray
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE)
CERTIFICATIONS	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.