

SERIAL DATA CABLES (Cont.)



Fig.1



Fig.2



Fig.3



Fig.4

DB25 Series

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Protocol | Length (Feet) | Color | Cable |
|-----------------|---------------|---------------|---------------------------------|----------|---------------|-------|-------------|
| 45-371 | | 1 | DB25 (Female)/DB25 (Female) | RS-232 | 6 | Putty | 25 x 28 AWG |
| 45-373 | | 1 | DB25 (Female)/DB25 (Female) | RS-232 | 10 | Putty | 25 x 28 AWG |
| 45-372 | | 1 | DB25 (Female)/DB25 (Female) | RS-232 | 15 | Putty | 25 x 28 AWG |
| 45-358 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 2 | Putty | 25 x 28 AWG |
| 45-379 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 6 | Putty | 25 x 28 AWG |
| 45-374 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 10 | Putty | 25 x 28 AWG |
| 45-1555 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 15 | Putty | 25 x 28 AWG |
| 45-375 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 25 | Putty | 25 x 28 AWG |
| 45-355 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 50 | Putty | 25 x 28 AWG |
| 45-356 | | 1&2 | DB25 (Female)/DB25 (Male) | RS-232 | 100 | Putty | 25 x 28 AWG |
| 45-1502 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 2 | Putty | 25 x 28 AWG |
| 45-376 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 6 | Putty | 25 x 28 AWG |
| 45-4363 | | 2 | DB25 (Male)/DB25 (Male)-Premium | RS-232 | 5 | Putty | 25 x 26 AWG |
| 45-4364 | | 2 | DB25 (Male)/DB25 (Male)-Premium | RS-232 | 10 | Putty | 25 x 26 AWG |
| 45-4366 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 25 | Putty | 25 x 28 AWG |
| 45-377 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 10 | Putty | 25 x 28 AWG |
| 45-378 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 25 | Putty | 25 x 28 AWG |
| 45-357 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 50 | Putty | 25 x 28 AWG |
| 45-369 | | 2 | DB25 (Male)/DB25 (Male) | RS-232 | 100 | Putty | 25 x 28 AWG |

DB37 Series

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Protocol | Length (Feet) | Color | Cable |
|-----------------|---------------|---------------|---------------------------|----------|---------------|-------|-------------|
| 45-463 | | 3&4 | DB37 (Male)/DB37 (Female) | RS-449 | 3 | Putty | 37 x 28 AWG |
| 45-466 | | 3&4 | DB37 (Male)/DB37 (Female) | RS-449 | 6 | Putty | 37 x 28 AWG |

SCSI CABLES, ADAPTERS & TERMINATORS



Fig.5



Fig.6



Fig.7



Fig.8



Fig.9



Fig.10

SCSI Cables

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Length (Feet) | Color | Conductor | Type |
|-----------------|---------------|---------------|--|---------------|-------|-------------------|--------------------|
| 45-846 | | 5&7 | Half Pitch CEN60 (Male)/CEN50 (Male), UL | 6 | Black | 25 Pairs x 28 AWG | IBM RS 6000-SCSI 1 |
| 45-863 | | 6&7 | DB25 (Male)/CEN50 (Male) | 3 | Putty | 19 Pairs x 26 AWG | Apple-SCSI 1 |
| 45-866 | | 6&7 | DB25 (Male)/CEN50 (Male) | 6 | Putty | 19 Pairs x 26 AWG | Apple-SCSI 1 |

SCSI 1 Cables

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Length (Feet) | Color | Conductor | Type |
|-----------------|---------------|---------------|-----------------------------|---------------|-------|-------------|---------------|
| 45-853 | | 7 | CEN50 (Male)/CEN50 (Male) | 3 | | 25 x 28 AWG | SCSI 1-SCSI 1 |
| 45-854 | | 7 | CEN50 (Male)/CEN50 (Male) | 3 | Putty | 50 x 28 AWG | SCSI 1-SCSI 1 |
| 45-873 | | 7&8 | CEN50 (Male)/CEN50 (Female) | 3 | | 25 x 28 AWG | SCSI 1-SCSI 1 |
| 45-856 | | 7 | CEN50 (Male)/CEN50 (Male) | 6 | Putty | 25 x 28 AWG | SCSI 1-SCSI 1 |

SCSI 2 Cables

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Length (Feet) | Color | Conductor | Type |
|-----------------|---------------|---------------|---|---------------|-------|-------------------|---------------|
| 45-1813 | | 9 | Half Pitch DB50 (Male)/Half Pitch DB50 (Male) | 1.5 | Putty | 25 Pairs x 28 AWG | SCSI 2-SCSI 2 |
| 45-890 | | 9 | Half Pitch DB50 (Male)/Half Pitch DB50 (Male) | 6 | Putty | 25 Pairs x 28 AWG | SCSI 2-SCSI 2 |

SCSI 3 Cables

| Retail Part No. | Bulk Part No. | Figure No.(s) | Description | Length (Feet) | Color | Conductor | Type |
|-----------------|---------------|---------------|---|---------------|-------|-------------------|---------------|
| 45-803 | | 10 | Half Pitch DB68 (Male)/(Male) | 3 | Putty | | SCSI 3-SCSI 3 |
| 45-877 | | 10 & 7 | Half Pitch DB68 (Male)/CEN50 (Male) | 6 | Putty | 25 Pairs x 28 AWG | SCSI 3-SCSI 1 |
| 45-905 | | 9 & 7 | Half Pitch DB50 (Male)/CEN50 (Male) | 3 | Putty | 25 Pairs x 28 AWG | SCSI 3-SCSI 2 |
| 45-906 | | 10 & 9 | Half Pitch DB68 (Male)/Half Pitch DB50 (Male) | 3 | Putty | 25 Pairs x 28 AWG | SCSI 3-SCSI 2 |