

WAVE[®] LED UV MAGNIFIER



For illustrative purposes only.

The WAVE LED UV Magnifier is Luxo's most recent addition to its line of WAVE LED Magnifiers. Its UV light sources make it ideal for the inspection of conformal coatings as well as for the detailed inspection of welds, solder joints and other areas of stress concentration. Two dimmable 6W UV-A LED light sources allow individual left/right lighting control. Auto shutoff feature further ensures energy savings. Complete with a choice of a 3.5- (1.88X) or 5-diopter (2.25X) precision-ground white crown optical quality glass lens. No knobs to tighten, nothing to adjust - a flexible, self-balancing shade and hands-free neck design allows the lamp head to be secured in any position. A fully enclosed neck assembly and 45" reach heavy-duty internal-spring K-arm for environments where cleanliness and sanitation are sought. Edge clamp mount. Color: Light grey.

- Two dimmable 6W UV-A LEDs
- Auto shutoff
- 6.75" x 4.5" precision-ground white crown optical quality lens
- Die-cast aluminum construction
- 45" arm length
- Color: Light Grey
- Individual left/right lighting control
- Fully-enclosed neck design
- 3.5-diopter (1.88X) or 5-diopter (2.25X) magnification
- Heavy duty internal-spring K-arm
- Edge clamp mount
- 5-year warranty

Part No.	Description
WAL026408	WAVE LED UV Magnifier, 3.5-diopter lens, 45" arm, edge clamp
WAL026409	WAVE LED UV Magnifier, 5-diopter lens, 45" arm, edge clamp