

MI DRG. NO. 8777G REV. G


8777

TUNING TOOL (MOLDED)

FILE: AIROUT

NOTES

1. MATERIAL: POLYCARBONATE & SPRING STEEL
2. DIMENSIONS ARE IN INCHES
3. MAXIMUM DRIVING TORQUE 8.0 OZ. IN.



LEVEL	DATE	DRN.	CHK.	TAM	APP.	JHT	020-024
G	03/22/02	MLD	TAM	-	-	-	000-127
F	03/28/00	MLD	-	-	-	-	ECN

REVISIONS

DRN.	MLD	CHK.	TAM	APP.	JHT	SCALE
DATE	DATE	DATE	DATE	DATE	DATE	1" = 1"
03/28/00	04/03/00	04/03/00	04/03/00	04/03/00	04/03/00	.XX ± .015 .XXX ± .005

JOHANSON MANUFACTURING CORPORATION
 ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
 ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION



PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL