



hover to zoom; click to enlarge

PART#: TOOL-69

Chemistry:	Nickel Metal Hydride (NIMH)
Voltage:	14.4
Capacity:	2700mAh
Measurements:	4.1" x 3.7" x 3.6" 104.14mm x 93.98mm x 91.44mm

[Find a Distributor](#)

SPECIFICATIONS

Shipping Weight (oz)	29.4000
Manufacturer	Dantona
Warranty	6
UPC	72828602069
Length	4.1" (104.14mm)
Width	3.7" (93.98mm)
Height / Diameter	3.6" (91.44mm)
Voltage	14.4
mAh	2700
Number of Cells	12
Battery Chemistry	Nickel Metal Hydride (NIMH)
Rechargeable	Rechargeable
Battery Color	Black
Qty Per Package	1
Type of Cell	Cylindrical, Sub-C
Weight	29.4 oz

Compatible Batteries and Devices

[Batteries \(9\)](#)

[Devices \(17\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been sponsored or approved by any of such manufacturers. Any trademarks or model numbers listed in this catalog are identified for compatibility or cross-reference purposes only.