




Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.

Pin Assignment

P1		P2
(A4,B4,A9,B9)VBUS	Red	1
(A7)Dn1	White	2
(A6)Dp1	Green	3
(A1,B1,A12,B12)GND	Drain	4
(A5)CC	Brain	Shell

①	A0020100-00174	USB TYPE C~n DOWM Nickel Plated Shell	1	pcs
⑩	A0020100-00175	USB TYPE C~n UP Nickel Plated Shell~	1	pcs
⑨	A10-R042106	Copper Foil:W=5MM 25u	0.012	M
⑧	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M
⑦	A5-R047001	Transparent PE	16	g
⑥	A5-R047011	45P PVC Color:Sonw BLACK	6	g
⑤	B010-00880	USB 2.0 C Type Black Insulation Nickel Plated Shell With PCBA(Resistance10KΩ)	1	pcs
④	A6-R107047	USB2.0 AM Front Shell Nickel Plated Shell (L=26.14MM)	1	pcs
③	A6-R107048	USB2.0 AM Back Shell Nickel Plated Shell (OD:3.5~4.5mm)	1	pcs
②	A2-R029131	USB2.0 AM White Insulation Solder Type,G/F Plated Terminal	1	pcs
①	A4-R003522	NO UL 28AWG(11/0.10TC)*2C+20AWG(26/0.16TC+250D)*1C+E(26/0.16+250D)+AB(16/8/0.08TC 95%TC) OD:3.5MM BLACK NO MARK	2.0	M
NO		DESCRIPTION	Q'TY	UNIT

REV.	ECN	DESCRIPTION	DATE	NAME
TOLERANCE INCHES M/M				
.X	.015	.30		
.XX	.010	.10		
.XXX	.005	.05		
DRAWN BY		李敏		
CHECK BY				
APPD BY				
		CUSTOMER :	CPC	
		CUSTOMER P/N :	CS28709	
		SCALE	NONE	DRAWING NO. : C06026-00002
		UNIT	mm	
		DATE	2015.05.13	REV. A01 1/1