





Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.



⑧	A0020100-00174	USB TYPE C~n Back Nickel Plated Shell	1	pcs		版本	ECN编号	描述		日期	变更人	
⑦	A0020100-00175	USB TYPE C~n Front Nickel Plated Shell~	1	pcs			TOLERANCE INCHES M/M		TITLE: USB2.0 CM TO AF CABLE L=2M			
⑥	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M			. X	. 015				. 30
⑤	A5-R047001	45P PVC Color:Sonw BLACK	16	g			. XX	. 010				. 10
④	A5-R047011	Transparent PE	6	g			. XXX	. 005				. 05
③	B010-00880	USB 2.0 C Type Black Insulation Nickel Plated Shell With PCBA(Resistance10KΩ)	1	pcs	DRAWN BY	李敏		CUSTOMER :		CPC		
②	A2-R029145	USB2.0 AF White Insulation Solder G/F Plated Terminal no edge Take to mould	1	pcs				CUSTOMER P/N :		CS28712		
①	A4-R003522	NO UL 28AWG(11/0.10TC)*2C+20AWG(26/0.16TC+250D)*1C+E(26/0.16+250D)+AB(16/8/0.08TC 95%TC) OD:3.5MM black no mark	1.98	M	CHECK BY			SCALE	NONE	DRAWING NO. : C06026-00005	REV. A01	
								UNIT	mm		1/1	
								DATE	2015.05.13			
NO		DESCRIPTION			APPD BY							