


Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.

Pin Assignment



⑧	A0020100-00173	USB TYPE C~n DOWM Nickel Plated Shell	1	pcs					
⑦	A0020100-00172	USB TYPE C~n UP Nickel Plated Shell~	1	pcs					
⑥	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M					
⑤	A5-R047001	Transparent PE	16	g					
④	A5-R047011	45P PVC Color:Sonw BLACK	6	g					
③	B010-00871	USB 2.0 C Type Black Insulation Nickel Plated Shell With PCBA(Resistance5.1KΩ)	1	pcs					
②	A2-R025089	MINI USB 5P4) after five welding line three type black rubber core iron shell plating nickel	1	pcs					
①	A4-R005013	NO-UL 30AWG (19/0.06TC)*2C+24AWG (26/0.1TC+250Dnylon)*1C+3E (19/0.05TC+250Dnylon)+AB (16/9/0.06TC 95%TC) OD:3.0MM PVC BLACK NO MARK	1.0	M					
NO		DESCRIPTION	Q'TY	UNIT					

版本	ECN编号	描述	日期	变更人
TOLERANCE				
INCHES				
M/M				
. X	.015	.30		
. XX	.010	.10		
. XXX	.005	.05		
DRAWN BY		李敏	CUSTOMER : CPC	
CHECK BY			CUSTOMER P/N : CS28719	
APPD BY			SCALE	NONE
			UNIT	mm
			DATE	2015.05.13
			DRAWING NO. :	C06026-00012
			REV.	A
				1/1