


CUSTOMER	CPC
PRODUCT NO.	CS287**Series
HENTEK NO.	HK-USB3.1BMC02-*Series



SIDE:A


SIDE:B

NOTE:

- (1). Cable Spec: (30AWG*1P+DAM)*2+30AWG*1P+28AWG*2C
Jacket Material:PVC OD:4.6 ± 0.2mm
Colour: Black
- (2). Connector A: USB3.1 C MALE Solder type
Insulation:Black
Contacts:Gold Plated
Shell:Nickel Plated
- (3). Connector B: USB3.1 MICRO B MALE Solder type
Insulation:Blue
Contacts:Gold Plated
Shell:Nickel Plated
- (4). Over Mold Colour: PVC-Black
- (5). Parameter Settings: CT-8681FA
1. Insulation Resistance:5MΩ (MIN.)
2. Conductive Resistance:2.0Ω (MAX.)
- (6). 100% OPEN, SHORT&MISWIRE TEST
- (7). PACKING:PEBAG PACKING.

<u>SIDE:A</u>		<u>SIDE:B</u>
USB CM		Micro 3.1BM
A4+B4+A9+B9	red	1
A6	white	3
A7	green	2
A1+B1+A12+B12	black	5+8
A2	blue	10
A3	yellow	9
A1+B1+A12+B12	drain	5+8
B10	orange	6
B11	purple	7
A1+B1+A12+B12	drain	5+8
Shell	braid	Shell

PIN OUT: (5)



PACKING: (7)

GENERAL TOLERANCES (UNLESS SPECIFIED)							
LENGTH: X. ± 1 .X ± 0.2 .XX ± 0.10 ANGLE: X° . ± 1° .X° ± 0° 30'	UNIT: mm	REV: 0/A			NAME	USB3.1 C MALE/MICRO B MALE	
	DRAWING	XIAODENG	2015/5/21	S. P. NO.	HT-6491		
	CHECK			P. O. NO.		DWG. NO.	
	APPROVE			SIZE		PAGE	1/1

00	NEW	2015/5/21
REV	DESCRIPTION	DATE