




RE920C64/2LF

- Extender card for 19"-systems DIN 41612 C64 a+c
- Epoxy fibre-glass FR4 1.50 mm
- Single-sided 70 µm CU
- Solder stop mask
- Component print
- Microswitches soldered with two measuring posts for each continuous strip
- Signalling line pin 2 - 31
- Large signalling line pin 1 + 32
- Switching voltage 10 mV - 60 V
- Switching current 0.3 A at 24 V
- Rest current at 20° C max. 6 A
- Contact resistance 30 mOhm
- Extender card: 100% electronically tested
- Size 100.00 x 278.70 mm (132.50 x 330.70 mm with handle)

ver.20150504